

**WQL 2 WF10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

|            |  |
|------------|--|
| Version    | Bolt-type screw terminals, Cross-connector, Number of poles: 2 |
| Order No.  | <a href="#">1781010000</a>                                     |
| Type       | WQL 2 WF10   |
| GTIN (EAN) | 4032248219421  |
| Qty.       | 5 items  |

### Technical data

#### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

#### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 4 mm    | Depth (inches)  | 0.1575 inch |
| Height     | 61.8 mm | Height (inches) | 2.4331 inch |
| Width      | 25 mm   | Width (inches)  | 0.9842 inch |
| Net weight | 48.01 g |                 |             |

#### Temperatures

|                     |                |                     |               |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

#### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

#### Material data

|                |               |        |      |
|----------------|---------------|--------|------|
| Basic material | Copper - zinc | Colour | grey |
|----------------|---------------|--------|------|

#### Additional technical data

|                |                 |                          |    |
|----------------|-----------------|--------------------------|----|
| Type of fixing | when screwed in | Explosion-tested version | No |
|----------------|-----------------|--------------------------|----|

#### Dimensions

|                 |          |
|-----------------|----------|
| Pitch in mm (P) | 33.80 mm |
|-----------------|----------|

#### General

|                 |   |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

#### Rating data

|                 |       |
|-----------------|-------|
| Nominal current | 269 A |
|-----------------|-------|

#### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |