

**VG M25 - K 68**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**


In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

**General ordering data**

Version	VG K (standard plastic cable gland), Cable glands, straight, M 25, 10 mm, OD min. 13 - OD max. 18 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	<a href="#">1772310000</a>
Type	VG M25 - K 68
GTIN (EAN)	4032248129973
Qty.	25 items

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Height	37 mm	Height (inches)	1.4567 inch
Length	47 mm	Length (inches)	1.8504 inch
Net weight	22.1 g		

**Temperatures**

Operating temperature -40 °C...100 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
REACH SVHC No SVHC above 0.1 wt%

**Certificate numbers cable gland**

Certificate no. cable gland (UL)	E-199260 - BM 15	Certificate no. cable gland (cULus)	E-199260 - BM 15
Approval conditions	DNV, UL, cULus		

**General information**

Outer cable diameter, max.	18 mm	Outer cable diameter, min.	13 mm
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Tightening torque	3.5 Nm
Silicone	No	UL 94 flammability rating	V-2
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Halogen	Yes
Standards	EN/IEC 62444	AF size 1	33 mm
AF size	33 mm	Protection degree	IP67, IP68 - 5 bar (30 min.)
Cable gland	metric	Basic material	Polyamide 6
Seal insert	CR	External thread	M 25
Length of thread	10 mm	Torque for cap nut, max.	6.00 Nm
Torque for lock nut, min.	3.00 Nm	Protection class (UL)	Type 4X
Torque for connecting adapter, max.	4.00 Nm	Torque for connecting adapter, min.	3.00 Nm
Torque for cap nut, min.	5.00 Nm	Torque for lock nut, max.	4.00 Nm

**Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

## VG M25 - K 68

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Plastic lock nuts, grey



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	SKMU M25 - K GR	Version	
Order No.	<a href="#">1772470000</a>	SKMU PA (plastic locknut), Locknut, M 25, 6 mm, Polyamid 6 (PA6 -	
GTIN (EAN)	4032248130214	GF30)	
Qty.	100 ST		

## Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	GWDR M25-NP	Version	
Order No.	<a href="#">1736250000</a>	GWDR NP (flat gasket - neoprene), Sealing ring, M 25, Neoprene	
GTIN (EAN)	4008190956042		
Qty.	100 ST		

## Polyethylene flat gasket - GWDR PO



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	GWDR M25-PO	Version	
Order No.	<a href="#">1777950000</a>	GWDR PO (flat gasket - polyethylene), Sealing ring, M 25,	
GTIN (EAN)	4032248158218	Polyethylene	
Qty.	50 ST		