

HDC-C-HD-B-LWL1.0POF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Fibre optic cables guarantee transmission that is non-interacting and disturbance-free.

The new fibre optic contacts can now also be used in heavy-duty connectors. Their shape corresponds to that of our proven HD contacts, for connecting conventional copper wires. Accordingly, they can be assembled in existing connectors of the HD series, as well as being suitable for use with the ConCept modular system.

It is even possible to connect fibre-optic wires and copper wires in a single connector.

General ordering data

Version	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Female, Conductor cross-section, max.: 1, turned, Copper alloy
Order No.	1773640000
Type	HDC-C-HD-B-LWL1.0POF
GTIN (EAN)	4032248142743
Qty.	10 items

HDC-C-HD-B-LWL1.0POF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Diameter	3.5 mm	Net weight	0.9 g
----------	--------	------------	-------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

General data

Contact diameter, male Ø	1.6 mm	Stripping length, rated connection	14 mm
Type of connection	Crimp connection	Version insert	HD, HDD, HQ, MixMate
Conductor cross-section, max.	1 mm ²	Conductor cross-section, min.	1 mm ²
Surface finish	silver	Plugging cycles	≥ 500
Type	Female	Basic material	Copper alloy
Production methods	turned	Cross-section for connected wire	1 - 1 mm ²
Material of contact	Copper alloy		

Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

HDC-C-HD-B-LWL1.0POF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

