


## LM WO 15/140 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

### General ordering data

Version	LaserMark, Conductor and cable markers, 16.2 - 36.4 mm, 15 x 140 mm, white
Order No.	<a href="#">1773880000</a>
Type	LM WO 15/140 WS
GTIN (EAN)	4032248144501
Qty.	10 items

## LM WO 15/140 WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	140 mm	Width (inches)	5.5118 inch
Net weight	10.2 g		

### Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Adhesive	Acrylate	
Material colour according to resistance code	9	
Number per sheet	26	
Type of printing	neutral	
Version	Self-adhesive	
Width	140 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	No	
Basic material	Polyester film	
Printed characters	without	
Number of markers per packaging unit	260	
Number of markers per packaging unit	Form of supply	Label sheet
	Number of combinations per packaging unit	10
	Number of markers per combination	26
Size of labelling field	15 x 70 mm	
Number of markers per combination	1 Label sheet = 26 Conductor and cable markers	
Operating temperature range	-40...150 °C	

### Conductor and cable markers

Halogen	No	Conductor cross-section, max.	150 mm <sup>2</sup>
Conductor cross-section, min.	70 mm <sup>2</sup>	Conductor O.D., max.	36.4 mm
Conductor O.D., min.	16.2 mm	Text field width	14.98 mm
Text field height	70 mm	Conductor O.D.	16.2 - 36.4 mm
Cross-section for connected wire	70 - 150 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

