

WSMH 288MM

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

General ordering data

| | |
|------------|---|
| Version | Stainless steel markers, Conductor and cable markers, 14 - 79 mm, 288 x 11 mm, silver |
| Order No. | 1774490000 |
| Type | WSMH 288MM |
| GTIN (EAN) | 4032248149285 |
| Qty. | 50 items |

WSMH 288MM

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| RoHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|--------------|
| Depth | 0.3 mm | Depth (inches) | 0.0118 inch |
| Height | 288 mm | Height (inches) | 11.3386 inch |
| Width | 11 mm | Width (inches) | 0.4331 inch |
| Net weight | 9.38 g | | |

Temperatures

| | |
|-----------------------------|--------|
| Operating temperature range | 250 °C |
|-----------------------------|--------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | |
|--------------------------------------|--|----------------|
| Type of printing | neutral | |
| Width | 11 mm | |
| Operating temperature range, max. | 250 °C | |
| Colour | silver | |
| Basic material | Stainless steel 1.4404 | |
| Printed characters | without | |
| Number of characters | 46 | |
| Number of markers per packaging unit | Form of supply | Component part |
| Number of markers per combination | 1 Component part = Conductor and cable markers | |
| Operating temperature range | 250 °C | |
| Number per roll | 50 | |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|----------------------------------|--------------------------|
| Conductor cross-section, max. | 500 mm ² | Conductor cross-section, min. | 16 mm ² |
| Conductor O.D., max. | 79 mm | Conductor O.D., min. | 14 mm |
| Conductor O.D. | 14 - 79 mm | Cross-section for connected wire | 16 - 500 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |