

WSMH 84MM**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

General ordering data

Version	Stainless steel markers, Conductor and cable markers, 14 - 79 mm, 84 x 11 mm, silver
Order No.	1774520000
Type	WSMH 84MM
GTIN (EAN)	4032248149315
Qty.	50 items

WSMH 84MM

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.0118 inch
Height	84 mm	Height (inches)	3.3071 inch
Width	11 mm	Width (inches)	0.4331 inch
Net weight	2.73 g		

Temperatures

Operating temperature range	250 °C
-----------------------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral
Width	11 mm
Operating temperature range, max.	250 °C
Colour	silver
Basic material	Stainless steel 1.4404
Printed characters	without
Number of characters	12
Number of markers per packaging unit	Form of supply
Number of markers per combination	1 Component part = Conductor and cable markers
Operating temperature range	250 °C
Number per roll	50

Conductor and cable markers

Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²
Conductor O.D., max.	79 mm	Conductor O.D., min.	14 mm
Conductor O.D.	14 - 79 mm	Cross-section for connected wire	16 - 500 mm ²

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		