


SAI-8-F 5P 15M 0.5/1.0U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



M12 distributors are available in various versions. The 4, 6 or 8 M12 slots are in 4 or 5 pole design. The group outlet is designed as a fixed cable version, hood version for connection by the user, or with M23. Special versions are also available. For instance, there are 1-to-1 distributors for use with any connection types, or distributors approved for Ex Zone 1.

General ordering data

| | |
|------------|---|
| Version | Fixed cable version, M12, 30 V, A-coded, LED: Yes, LED initiator: Yes, Wiring type: PNP, 15 m |
| Order No. | 1784510000 |
| Type | SAI-8-F 5P 15M 0.5/1.0U |
| GTIN (EAN) | 4032248190706 |
| Qty. | 1 items |

SAI-8-F 5P 15M 0.5/1.0U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform
UL File Number Search [UL Website](#)
Certificate No. (cURus) E141197

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 25 mm | Height (inches) | 0.9842 inch |
| Net weight | 2548 g | | |

Temperatures

Operating temperature -20 - 80°C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Connection data

| | | | |
|----------------------------|--------|--------------------|---------------------|
| Sheathing stripping length | 100 mm | Distributor outlet | Fixed cable version |
|----------------------------|--------|--------------------|---------------------|

Electrical data

| | | | |
|--------------------------------|------|---|-------|
| Rated voltage, min. | 10 V | Rated voltage, max. | 30 V |
| Test voltage | 1 kV | Max. current-carrying capacity per slot | 4 A |
| Total current | 9 A | Current per signal | 2 A |
| Electrical isolation available | No | Insulation resistance | 109 Ω |

General technical data

| | | | |
|-------------------------------------|-------|-----------------------------|---------|
| Protection degree | IP68 | Plug-in station coding | A-coded |
| Number of poles | 5 | Number of contact sockets | 8 |
| Connection thread | M12 | Pollution severity | 3 |
| Fire behaviour | V-0 | Plugging cycles | ≤ 50 |
| LED | Yes | LED initiator | Yes |
| LED colour for indicating operation | green | LED colour for I/O function | yellow |

Material data

| | | | |
|-----------------------|--------------------|--------------------------|----------------|
| Housing main material | Pocan | Material of distributor | Plastic |
| Housing colour | grey, RAL 7032 | Hood sealing material | Viton |
| Screw socket | Nickel-plated CuZn | Contact material | CuZn |
| Contact surface | Gold-plated | Contact carrier material | PBT (UL 94 V0) |

Technical data cable

| | | | |
|-----------------|---------|------------------------------|---------------------|
| Number of poles | 5 | Sheathing colour | Deep black |
| O.D. | 12.3 mm | Bending radius, min., moving | 10 x cable diameter |

SAI-8-F 5P 15M 0.5/1.0U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|----------------------------------|--|-----------------------------------|--|
| Bending radius, min., stationary | 5 x cable diameter | Wire cross section (Print/Online) | 16 x 0.5 mm ² + 3 x 1.0 mm ² |
| Colour coding | blue, brown, Green/yellow, yellow, grey, green, white, pink, red, black, violet, grey / pink, red / blue, white / green, brown / green, white / yellow, Yellow / brown, grey / brown | Cable length | 15 m |
| Suitable for cable carriers | Yes | Armoured line | 16 x 0,5 mm ² + 3 x 1 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002585 | ETIM 9.0 | EC002585 |
| ETIM 10.0 | EC002585 | ECLASS 14.0 | 27-44-01-08 |
| ECLASS 15.0 | 27-44-01-08 | | |

SAI-8-F 5P 15M 0.5/1.0U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Drawings

www.weidmueller.com

Dimensioned drawing



Wiring diagram

