

**SAIBGZ-M-4A-6/8-M12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

Tension-clamp connection delivers excellent functional security and reduced installation times. With this technology the conductor is plugged into the tension clamp without a wire-end ferrule (optionally with wire-end ferrule). The connection between the conductor and tension clamp is vibration-resistant and boasts long-term stability.

**General ordering data**

Version	Field attachable connector, M12
Order No.	<a href="#">1784740002</a>
Type	SAIBGZ-M-4A-6/8-M12
GTIN (EAN)	4032248647965
Qty.	1 items

## SAIBGZ-M-4A-6/8-M12

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



RoHS Conform

## Dimensions and weights

Net weight 40.48 g

## Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, Imidazolidine-2-thione 96-45-7

SCIP bcee35cf-c0f5-43d2-8daf-65ab0d08641a

## Technical data customisable plug-in connectors

Number of poles	4	Coding	A-coded
Contact surface	Gold-plated	Type of connection	Tension-clamp connection
Housing main material	PA	Insulation resistance	108 Ω
Cable diameter, max.	8 mm	Cable diameter, min.	6 mm
Conductor cross-section, max.	0.5 mm <sup>2</sup>	Conductor cross-section, min.	0.25 mm <sup>2</sup>
Nominal voltage	250 V	Nominal current	4 A
Protection degree	IP67	Plugging cycles	≥ 100
Pollution severity	3	Gender of contact	Female
Shield connection	Yes	Threaded ring material	Diecast zinc
Temperature range of housing	-40 ... +85 °C	Connection cross-section, max.	0.5 mm <sup>2</sup>
Connection cross-section, min.	0.14 mm <sup>2</sup>		

## General Info

Number of poles	4	Connection 1	M12
Connection 2	Tension-clamp	Housing main material	PA
Connection thread	M12	Contact surface	Gold-plated
Protection degree	IP67	Plugging cycles	≥ 100

## Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

**SAIBGZ-M-4A-6/8-M12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Pole scheme**