

**WQL 2 WF10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Bolt-type screw terminals, Cross-connector, Number of poles: 2
Order No.	<a href="#">1781010000</a>
Type	WQL 2 WF10
GTIN (EAN)	4032248219421
Qty.	5 items

### Technical data

#### Approvals

ROHS	Conform
------	---------

#### Dimensions and weights

Depth	4 mm	Depth (inches)	0.1575 inch
Height	61.8 mm	Height (inches)	2.4331 inch
Width	25 mm	Width (inches)	0.9842 inch
Net weight	48.01 g		

#### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

#### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

#### Material data

Basic material	Copper - zinc	Colour	grey
----------------	---------------	--------	------

#### Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
----------------	-----------------	--------------------------	----

#### Dimensions

Pitch in mm (P)	33.80 mm
-----------------	----------

#### General

Number of poles	2
-----------------	---

#### Rating data

Nominal current	269 A
-----------------	-------

#### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		