



**BLL 5.00/08/180 4.5SN BK BX****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The best-known plug-in system on the market offers users an almost inexhaustible range of options and results in a pluggable solution for virtually every application.

**General ordering data**

|              |                                                                                                                                                                |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, female header, closed side, THT solder connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): 4.5 mm, tinned, black, Box |
| Order No.    | <a href="#">1781920000</a>                                                                                                                                     |
| Type         | BLL 5.00/08/180 4.5SN BK BX                                                                                                                                    |
| GTIN (EAN)   | 4032248173846                                                                                                                                                  |
| Qty.         | 42 items                                                                                                                                                       |
| Product data | IEC: 400 V / 23 A<br>UL: 300 V / 15 A                                                                                                                          |
| Packaging    | Box                                                                                                                                                            |

## BLL 5.00/08/180 4.5SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



|                       |                            |
|-----------------------|----------------------------|
| ROHS                  | Conform                    |
| UL File Number Search | <a href="#">UL Website</a> |
| Certificate No. (UR)  | E60693                     |

## Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 8.33 g |
|------------|--------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## System specifications

|                                                   |                                     |                                              |                              |
|---------------------------------------------------|-------------------------------------|----------------------------------------------|------------------------------|
| Product family                                    | OMNIMATE Signal - series BL/SL 5.00 | Type of connection                           | Board connection             |
| Mounting onto the PCB                             | THT solder connection               | Pitch in mm (P)                              | 5.08 mm                      |
| Pitch in inches (P)                               | 0.200 "                             | Outgoing elbow                               | 180°                         |
| Number of poles                                   | 8                                   | Number of solder pins per pole               | 2                            |
| Solder pin length (l)                             | 4.5 mm                              | Solder pin length tolerance                  | +0.1 / -0.2 mm               |
| Solder pin dimensions                             | 0.4 x 1.00 mm                       | Solder eyelet hole diameter (D)              | 1.3 mm                       |
| Solder eyelet hole diameter tolerance (D)+ 0,1 mm |                                     | L1 in mm                                     | 35.56 mm                     |
| L1 in inches                                      | 1.400 "                             | Number of rows                               | 1                            |
| Pin series quantity                               | 1                                   | Touch-safe protection acc. to DIN VDE 57 106 | Safe from back-of-hand touch |
| Touch-safe protection acc. to DIN VDE 0470        | IP20 plugged                        | Protection degree                            | IP20                         |
| Volume resistance                                 | ≤5 mΩ                               | Can be coded                                 | Yes                          |
| Plugging cycles                                   | 25                                  | Plugging force/pole, max.                    | 5 N                          |
| Pulling force/pole, max.                          | 5 N                                 |                                              |                              |

## Material data

|                                       |                            |                                       |                            |
|---------------------------------------|----------------------------|---------------------------------------|----------------------------|
| Insulating material                   | PBT GF                     | Colour                                | black                      |
| Colour chart (similar)                | RAL 9011                   | Insulating material group             | IIla                       |
| Comparative Tracking Index (CTI)      | ≥ 175, ≥ 200               | Insulation resistance                 | 108 Ω                      |
| Moisture Level (MSL)                  |                            | UL 94 flammability rating             | V-0                        |
| Contact material                      | Copper alloy               | Contact surface                       | tinned                     |
| Layer structure of solder connection  | 4...6 µm Sn hot-dip tinned | Layer structure of plug contact       | 4...6 µm Sn hot-dip tinned |
| Storage temperature, min.             | -40 °C                     | Storage temperature, max.             | 70 °C                      |
| Operating temperature, min.           | -50 °C                     | Operating temperature, max.           | 100 °C                     |
| Temperature range, installation, min. | -25 °C                     | Temperature range, installation, max. | 100 °C                     |

## Rated data acc. to IEC

|                                               |                        |                                               |      |
|-----------------------------------------------|------------------------|-----------------------------------------------|------|
| tested acc. to standard                       | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C) | 23 A |
| Rated current, max. number of poles (Tu=20°C) | 16 A                   | Rated current, min. number of poles (Tu=40°C) | 20 A |

**BLL 5.00/08/180 4.5SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Technical data**

|                                                                           |       |                                                                       |                   |
|---------------------------------------------------------------------------|-------|-----------------------------------------------------------------------|-------------------|
| Rated current, max. number of poles (Tu=40°C)                             | 14 A  | Rated voltage for surge voltage class / pollution degree II/2         | 400 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 V   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV  | Short-time withstand current resistance                               | 3 x 1s with 120 A |

**Rated data acc. to CSA**

|                                   |                                                                        |                                   |                |
|-----------------------------------|------------------------------------------------------------------------|-----------------------------------|----------------|
| Institute (CSA)                   | CSA                                                                    | Certificate No. (CSA)             | 200039-1121690 |
| Rated voltage (Use group B / CSA) | 300 V                                                                  | Rated voltage (Use group D / CSA) | 300 V          |
| Rated current (Use group B / CSA) | 15 A                                                                   | Rated current (Use group D / CSA) | 10 A           |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |                                   |                |

**Rated data acc. to UL 1059**

|                                       |                                                                        |                                       |        |
|---------------------------------------|------------------------------------------------------------------------|---------------------------------------|--------|
| Institute (UR)                        | UR                                                                     | Certificate No. (UR)                  | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V                                                                  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 15 A                                                                   | Rated current (Use group D / UL 1059) | 10 A   |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

**Packing**

|           |           |            |           |
|-----------|-----------|------------|-----------|
| Packaging | Box       | VPE length | 350.00 mm |
| VPE width | 136.00 mm | VPE height | 31.00 mm  |

**Important note**

|                |                                                                                                                                                                                                                                                                                                                                                                           |  |  |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                |  |  |
| Notes          | <ul style="list-style-type: none"> <li>In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |  |  |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002637    | ETIM 9.0    | EC002637    |
| ETIM 10.0   | EC002637    | ECLASS 14.0 | 27-46-02-01 |
| ECLASS 15.0 | 27-46-02-01 |             |             |

## Drawings

### Product image

