

**SAISGI-P-3A-3.2/5.4-M8****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M8 round plug-in connectors are particularly suited to applications where space is limited.

The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

**General ordering data**

Version	Field attachable connector, M8
Order No.	<a href="#">1784040001</a>
Type	SAISGI-P-3A-3.2/5.4-M8
GTIN (EAN)	4032248429998
Qty.	1 items

## SAISGI-P-3A-3.2/5.4-M8

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Diameter	11.5 mm	Net weight	13 g
----------	---------	------------	------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

## Technical data customisable plug-in connectors

Number of poles	3	Coding	A-coded
Contact surface	Gold-plated	LED	No
Type of connection	Insulation displacement connection	Housing main material	Zinc diecast, Polyamide
Insulation resistance	108 Ω	Cable diameter, max.	5.1 mm
Cable diameter, min.	2.5 mm	Conductor cross-section, max.	0.34 mm <sup>2</sup>
Conductor cross-section, min.	0.14 mm <sup>2</sup>	Nominal voltage	32 V
Nominal current	4 A	Protection degree	IP67
Plugging cycles	≥ 50	Pollution severity	3
Gender of contact	Male	Shield connection	No
Threaded ring material	Diecast zinc	Temperature range of housing	-40 ... +85 °C

## Standards

Connector standard	IEC 61076-2-104
--------------------	-----------------

## Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		