

HDC 07A TWLU 1M20G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Installation size: 1, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 20
Order No.	1788510000
Type	HDC 07A TWLU 1M20G
GTIN (EAN)	4032248206049
Qty.	1 items

HDC 07A TWLU 1M20G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Dimensions and weights

Depth	37.3 mm	Depth (inches)	1.4685 inch
Height	50 mm	Height (inches)	1.9685 inch
Width	36.5 mm	Width (inches)	1.437 inch
Net weight	12.32 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	2f94735a-9fba-4903-842f-4fb9aa902310

Chemical resistance	Substance	Acetone
	Chemical resistance	Conditionally resistant
Substance	Drilling oil	
Chemical resistance	Resistant	
Substance	Diesel	
Chemical resistance	Resistant	
Substance	Ethyl alcohol	
Chemical resistance	Resistant	
Substance	Transmission oil	
Chemical resistance	Resistant	
Substance	Hydraulic oil	
Chemical resistance	Resistant	
Substance	Coolant	
Chemical resistance	Resistant	
Substance	Petroleum benzine	
Chemical resistance	Resistant	
Substance	Sweat	
Chemical resistance	Resistant	
Substance	Premium gasoline	
Chemical resistance	Conditionally resistant	
Substance	Water	
Chemical resistance	Resistant	
Substance	UV	
Chemical resistance	Unstable	
Substance	Ozone	
Chemical resistance	Unstable	

Dimensions

Cable entry	w. thread	Width housing C	26.8 mm
Total length housing	37.3 mm	Height of housing B	50 mm

HDC 07A TWLU 1M20G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

General data

Tightening torque	0.5 Nm	UL 94 flammability rating	V-0
Housing main material	Plastic	Protection degree	IP65, in plugged condition
EMC housings	No		

Version

Size of cable entries	M 20	Top part/bottom part/lid	upper part
Cover	without cover	Tightening torque	0.5 Nm
Number of cable entry on top	0	Number of cable entry sideways	1
Design of housing	Cable entry from side, Plug housing	Design of locking system	Side-locking clamp on lower side
Design	Standard	Installation size	1
Cable entry	w. thread	Type	Plug
Clamp version	Side-locking clamp	Sealing	no sealing
Internal thread	M 20	Colour (RAL)	RAL 1001
BG	1	Suitable for ModuPlug®	No


Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

HDC 07A TWLU 1M20G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

HDC 07A TWLU 1M20G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

IP67 version w/o approval



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Type	VG M20-K67 10-14	Version
Order No.	1909700000	VG K (standard plastic cable gland), Cable glands, straight, M 20, 10
GTIN (EAN)	4032248536627	mm, OD min. 10 - OD max. 14 mm, Polyamide 6
Qty.	50 ST	

IP68 version



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Type	VG M20-1/K68	Version
Order No.	1772300000	VG K (standard plastic cable gland), Cable glands, straight, M 20, 10
GTIN (EAN)	4032248129966	mm, OD min. 6 - OD max. 12 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Qty.	50 ST	

IP67 version w/o approval



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Type	VG M20-K67 6-12	Version
Order No.	1909690000	VG K (standard plastic cable gland), Cable glands, straight, M 20, 10
GTIN (EAN)	4032248536610	mm, OD min. 6 - OD max. 12 mm, Polyamide 6
Qty.	50 ST	

HDC 07A TWLU 1M20G

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

IP68 version with spiral antikink protection



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Type	VG M20-K68 SKS 10-14	Version
Order No.	1776720000	VG K SZS (standard plastic cable gland with anti-kink coils), Cable
GTIN (EAN)	4032248156146	glands, straight, M 20, 15 mm, OD min. 10 - OD max. 14 mm,
Qty.	25 ST	Polyamide 6
Type	VG M20-K68 SKS 6-12	Version
Order No.	1778860000	VG K SZS (standard plastic cable gland with anti-kink coils), Cable
GTIN (EAN)	4032248161874	glands, straight, M 20, 11 mm, OD min. 6 - OD max. 12 mm,
Qty.	50 ST	Polyamide 6