




Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image















1





The SC pin header has a perpendicular (standing) plugging direction in relation to the PCB. It is available in closed (G) and screw flange (F) versions.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

General ordering data

| Version | PCB plug-in connector, male header, closed side, THT solder connection, 3.81 mm, Number of poles: 10, 180°, Solder pin length (I): 3.2 mm, tinned, Pale green, Box | |
|--------------|---|--|
| Order No. | <u>1793670000</u> | |
| Туре | SC 3.81/10/180G 3.2SN GN BX | |
| GTIN (EAN) | 4032248230792 | |
| Qty. | 42 items | |
| Product data | IEC: 320 V / 17.5 A UL: 300 V / 11 A | |
| Packaging | Вох | |



SC 3.81/10/180G 3.2SN GN BX



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

| Approvals | S |
|-----------|---|
|-----------|---|

| Approvals | c FL *us |
|-------------------------|-------------------|
| ROHS | Conform |
| UL File Number Search | <u>UL Website</u> |
| Certificate No. (cURus) | E60693 |

Dimensions and weights

| Depth | 7.1 mm | Depth (inches) | 0.2795 inch |
|--------------------------|-------------|-----------------|-------------|
| Height | 12.4 mm | Height (inches) | 0.4882 inch |
| Height of lowest version | 9.2 mm | Width | 39.5 mm |
| Width (inches) | 1.5551 inch | Net weight | 2.5 g |

Environmental Product Compliance

| Compliant without exemption | |
|-----------------------------|--|
| No SVHC above 0.1 wt% | |
| | and the second s |

System specifications

| Product family | OMNIMATE Signal - series BC/SC 3.81 | Type of connection | Board connection |
|--|---|---|------------------------------|
| Mounting onto the PCB | THT solder connection | Pitch in mm (P) | 3.81 mm |
| Pitch in inches (P) | 0.150 " | Outgoing elbow | 180° |
| Number of poles | 10 | Number of solder pins per pole | 1 |
| Solder pin length (I) | 3.2 mm | Solder pin length tolerance | 0 / -0.2 mm |
| Solder pin dimensions | d = 1.0 mm, Octagonal | Solder pin dimensions = d tolerance | 0 / -0,03 mm |
| Solder eyelet hole diameter (D) | 1.2 mm | Solder eyelet hole diameter tolerance (D)+ 0,1 mm | |
| L1 in mm | 34.29 mm | L1 in inches | 1.350 " |
| Number of rows | 1 | Pin series quantity | 1 |
| Touch-safe protection acc. to DIN VDE 57 106 | finger-safe unplugged/ back-of-hand-safe plugged | Touch-safe protection acc. to DIN VDE 0470 | IP20 plugged/ IP10 unplugged |
| Volume resistance | ≤5 mΩ | Can be coded | Yes |
| Plugging force/pole, max. | 7 N | Pulling force/pole, max. | 5 N |

Material data

| Insulating material | PA GF | Colour | Pale green |
|---------------------------------------|----------|---------------------------------------|--------------|
| Colour chart (similar) | RAL 6021 | Insulating material group | II |
| Comparative Tracking Index (CTI) | ≥ 550 | Moisture Level (MSL) | |
| UL 94 flammability rating | V-0 | Contact material | Copper alloy |
| Contact surface | tinned | Storage temperature, min. | -40 °C |
| Storage temperature, max. | 70 °C | Operating temperature, min. | -50 °C |
| Operating temperature, max. | 120 °C | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 120 °C | | |

Rated data acc. to IEC

| tested acc. to standard | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C) | 17.5 A |
|---|------------------------|---|--------|
| Rated current, max. number of poles (Tu=20°C) | 17.1 A | Rated current, min. number of poles (Tu=40°C) | 17.5 A |

Creation date 12.11.2025 02:29:46 MEZ

Catalogue status / Drawings 2



SC 3.81/10/180G 3.2SN GN BX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

| Rated current, max. number of poles 17.1 A | Rated voltage for surge voltage class / 320 V |
|--|--|
| (Tu=40°C) | pollution degree II/2 |
| Rated voltage for surge voltage class / 160 V pollution degree III/2 | Rated voltage for surge voltage class / 160 V pollution degree III/3 |
| Rated impulse voltage for surge voltage 2.5 kV class/ pollution degree II/2 | Rated impulse voltage for surge voltage 2.5 kV class/ pollution degree III/2 |
| Rated impulse voltage for surge voltage 2.5 kV class/ contamination degree III/3 | Short-time withstand current resistance 3 x 1s with 76 A |

Rated data acc. to CSA

| Rated voltage (Use group B / CSA) | 300 V | Rated current (Use group B / CSA) | 11 A |
|-----------------------------------|-------|-----------------------------------|------|
| Rated current (Use group D / CSA) | 10 A | | |

Rated data acc. to UL 1059

| Institute (cURus) | CURUS | Certificate No. (cURus) | E60693 |
|---------------------------------------|--|---------------------------------------|--------|
| Rated voltage (Use group B / UL 1059) | 300 V | Rated voltage (Use group D / UL 1059) | 300 V |
| Rated current (Use group B / UL 1059) | 11 A | Rated current (Use group D / UL 1059) | 10 A |
| Reference to approval values | Specifications are maximum values, details - | | |

Packing

| Packaging | Box | VPE length | 350.00 mm |
|-----------|-----------|------------|-----------|
| VPE width | 140.00 mm | VPE height | 34.00 mm |

Important note

| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request. |
|----------------|--|
| Notes | Additional variants on request Rated current related to rated cross-section & min. No. of poles. Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards. P on drawing = pitch |
| | In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or |

disengaged when live or under load Long term storage of the product with average temperature of 50 °C and maximum humidity

70%, 36 months

Classifications

| ETIM 6.0 | EC002637 | ETIM 7.0 | EC002637 |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002637 | ETIM 9.0 | EC002637 |
| ETIM 10.0 | EC002637 | ECLASS 9.0 | 27-44-04-02 |
| ECLASS 9.1 | 27-44-04-02 | ECLASS 10.0 | 27-44-04-02 |
| ECLASS 11.0 | 27-46-02-01 | ECLASS 12.0 | 27-46-02-01 |
| ECLASS 13.0 | 27-46-02-01 | ECLASS 14.0 | 27-46-02-01 |
| ECLASS 15.0 | 27-46-02-01 | | |

Creation date 12.11.2025 02:29:46 MEZ

3 Catalogue status / Drawings

SC 3.81/10/180G 3.2SN GN BX




Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany


www.weidmueller.com

Drawings

Product image



Dimensional drawing







Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Coding elements



Only connects what is supposed to be connected: the right connection at the right place.

Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase. The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery. Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible. The advantage: no troubleshooting during manufacture and no operational errors by the user.

General ordering data

| Туре | SC-SMT 3.81 KO GY BX | Version |
|------------|----------------------|---|
| Order No. | <u>1968900000</u> | PCB plug-in connector, Accessories, Coding element, grey, Number of |
| GTIN (EAN) | 4032248772865 | poles: 6 |
| Qty. | 100 ST | |