

## WS 10/5 M MC NE WS


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text.

WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |   |
|------------|---|
| Version    | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, white |
| Order No.  | <a href="#">1792000000</a>  |
| Type       | WS 10/5 M MC NE WS  |
| GTIN (EAN) | 4032248223862   |
| Qty.       | 720 items   |

## WS 10/5 M MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 10 mm  | Height (inches) | 0.3937 inch |
| Width      | 5 mm   | Width (inches)  | 0.1968 inch |
| Net weight | 0.14 g |                 |             |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

### Environmental Product Compliance

|                          |                             |                 |  |
|--------------------------|-----------------------------|-----------------|--|
| RoHS Compliance Status   | Compliant without exemption |                 |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                 |  |
| Product Carbon Footprint | Cradle to gate              | 0.001 kg CO2eq. |  |

### General data

|  |   |           |  |
|--|---|-----------|--|
| Material colour according to resistance code | 9   |           |  |
| Width  | 5 mm  |           |  |
| UL 94 flammability rating                    | V-2   |           |  |
| Operating temperature range, max.            | 100 °C  |           |  |
| Operating temperature range, min.            | -40 °C  |           |  |
| Colour                                       | white   |           |  |
| Halogen                                      | No  |           |  |
| Basic material                               | Polyamide 66  |           |  |
| Colour of printing                           | black   |           |  |
| Printed characters                           | neutral   |           |  |
| Number of markers per packaging unit         | Form of supply  | MultiCard |  |
| compatible printer                           | <a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a> |           |  |
| Number of markers per combination            | 1 MultiCard = Terminal marker   |           |  |
| Operating temperature range                  | -40...100 °C  |           |  |
| Application/manufacturer                     | Weidmueller, Allen-Bradley  |           |  |

### Connector markers

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 5.00 mm |
|-----------------|---------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

**Drawings**



**Drawing**

