


WS 10/5 MC M SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

Similar to illustration

WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text.

WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/ or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

| | |
|------------|--|
| Version | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmüller, Allen-Bradley, To customer specification |
| Order No. | 1792010000 |
| Type | WS 10/5 MC M SDR |
| GTIN (EAN) | 4032248223879 |
| Qty. | 144 items |

WS 10/5 MC M SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| RoHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Height | 10 mm | Height (inches) | 0.3937 inch |
| Width | 5 mm | Width (inches) | 0.1968 inch |
| Net weight | 0.1 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|--------------------------|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |
| Product Carbon Footprint | Cradle to gate 0.002 kg CO ₂ eq. |

General data

| | | |
|--|-------------------------------|-----------|
| Material colour according to resistance code | 9 | |
| Orientation of print | horizontal and vertical | |
| Printing method | MC Laser | |
| Width | 5 mm | |
| UL 94 flammability rating | V-2 | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| Colour | To customer specification | |
| Basic material | Polyamide 66 | |
| Colour of printing | black | |
| Printed characters | Requires M-Print PRO File | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Number of markers per combination | 1 MultiCard = Terminal marker | |
| Operating temperature range | -40...100 °C | |
| Application/manufacturer | Weidmueller, Allen-Bradley | |

Connector markers

| | |
|-----------------|---------|
| Pitch in mm (P) | 5.00 mm |
|-----------------|---------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000761 | ETIM 9.0 | EC000761 |
| ETIM 10.0 | EC000761 | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 | | |

WS 10/5 MC M SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Similar to illustration**Drawing**