

**S2L-SMT 3.50/34/90LF 3.2SN BK BX**
**Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Do not use product for  
new developments

**Product image**


Similar to illustration

High-temperature-resistant, straight, 2-tier male connector for all common soldering methods. Optimised for automatic assembly. Packed in box or tape. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

**General ordering data**

|                      |                                                                                                                                                                    |
|----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version              | PCB plug-in connector, male header, Solder flange, THT/THR solder connection, 3.50 mm, Number of poles: 34, 90°, Solder pin length (l): 3.2 mm, tinned, black, Box |
| Order No.            | <a href="#">1795000000</a>                                                                                                                                         |
| Type                 | S2L-SMT 3.50/34/90LF 3.2SN BK BX                                                                                                                                   |
| GTIN (EAN)           | 4032248232451                                                                                                                                                      |
| Qty.                 | 24 items                                                                                                                                                           |
| Product data         | IEC: 160 V / 10 A<br>UL: 150 V / 10 A                                                                                                                              |
| Packaging            | Box                                                                                                                                                                |
| Delivery status      | This article will no longer be available in the future.                                                                                                            |
| Last order date      | 2028-12-31T00:00:00+01:00                                                                                                                                          |
| Alternative part no. | <a href="#">S2L-SMT 3.50/34/90LF 3.2SN BK BX</a>                                                                                                                   |

## S2L-SMT 3.50/34/90LF 3.2SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

## Dimensions and weights

|                          |             |                 |             |
|--------------------------|-------------|-----------------|-------------|
| Depth                    | 14.2 mm     | Depth (inches)  | 0.5591 inch |
| Height                   | 14.2 mm     | Height (inches) | 0.5591 inch |
| Height of lowest version | 10.8 mm     | Width           | 66.5 mm     |
| Width (inches)           | 2.6181 inch | Net weight      | 10.95 g     |

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## System specifications

|                                              |                                                     |                                            |                              |
|----------------------------------------------|-----------------------------------------------------|--------------------------------------------|------------------------------|
| Product family                               | OMNIMATE Signal - series B2L/S2L 3.50 - 2-row       | Type of connection                         | Board connection             |
| Mounting onto the PCB                        | THT/THR solder connection                           | Pitch in mm (P)                            | 3.50 mm                      |
| Pitch in inches (P)                          | 0.138 "                                             | Outgoing elbow                             | 90°                          |
| Number of poles                              | 34                                                  | Number of solder pins per pole             | 1                            |
| Solder pin length (l)                        | 3.2 mm                                              | Solder pin dimensions                      | d = 1.0 mm, Octagonal        |
| Solder eyelet hole diameter (D)              | 1.3 mm                                              | Solder eyelet hole diameter tolerance (D)+ | 0,1 mm                       |
| Outside diameter of solder pad               | 2.1 mm                                              | Template aperture diameter                 | 1.9 mm                       |
| L1 in mm                                     | 56.00 mm                                            | L1 in inches                               | 2.205 "                      |
| Number of rows                               | 1                                                   | Pin series quantity                        | 2                            |
| Touch-safe protection acc. to DIN VDE 57 106 | finger-safe unplugged/<br>back-of-hand-safe plugged | Touch-safe protection acc. to DIN VDE 0470 | IP20 plugged/ IP10 unplugged |
| Can be coded                                 | Yes                                                 | Plugging force/pole, max.                  | 3 N                          |
| Pulling force/pole, max.                     | 6 N                                                 |                                            |                              |

## Material data

|                                       |                           |                                       |                                  |
|---------------------------------------|---------------------------|---------------------------------------|----------------------------------|
| Insulating material                   | LCP GF                    | Colour                                | black                            |
| Colour chart (similar)                | RAL 9011                  | Insulating material group             | IIIb                             |
| Comparative Tracking Index (CTI)      | ≥ 175                     | Moisture Level (MSL)                  | 1                                |
| UL 94 flammability rating             | V-0                       | Contact material                      | Cu-alloy                         |
| Contact surface                       | tinned                    | Layer structure of solder connection  | 2...3 µm Ni / 5...7 µm Sn glossy |
| Layer structure of plug contact       | 2...5 µm Sn / 1...3 µm Ni | Storage temperature, min.             | -40 °C                           |
| Storage temperature, max.             | 70 °C                     | Operating temperature, min.           | -50 °C                           |
| Operating temperature, max.           | 100 °C                    | Temperature range, installation, min. | -30 °C                           |
| Temperature range, installation, max. | 100 °C                    |                                       |                                  |

**S2L-SMT 3.50/34/90LF 3.2SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data****Rated data acc. to IEC**

|                                                                           |                        |                                                                       |                  |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 10 A             |
| Rated current, max. number of poles (Tu=20°C)                             | 10 A                   | Rated current, min. number of poles (Tu=40°C)                         | 9 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 8.5 A                  | Rated voltage for surge voltage class / pollution degree II/2         | 160 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 125 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 50 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 1.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 1.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 77 A |

**Rated data acc. to CSA**

|                                   |                                                                        |                                   |                |
|-----------------------------------|------------------------------------------------------------------------|-----------------------------------|----------------|
| Institute (CSA)                   | CSA                                                                    | Certificate No. (CSA)             | 200039-1176845 |
| Rated voltage (Use group B / CSA) | 150 V                                                                  | Rated voltage (Use group C / CSA) | 50 V           |
| Rated voltage (Use group D / CSA) | 150 V                                                                  | Rated current (Use group B / CSA) | 5 A            |
| Rated current (Use group C / CSA) | 9.5 A                                                                  | Rated current (Use group D / CSA) | 9.5 A          |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |                                   |                |

**Rated data acc. to UL 1059**

|                                       |                                                                        |                                       |        |
|---------------------------------------|------------------------------------------------------------------------|---------------------------------------|--------|
| Institute (UR)                        | UR                                                                     | Certificate No. (UR)                  | E60693 |
| Rated voltage (Use group B / UL 1059) | 150 V                                                                  | Rated voltage (Use group C / UL 1059) | 50 V   |
| Rated current (Use group B / UL 1059) | 10 A                                                                   | Rated current (Use group C / UL 1059) | 10 A   |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

**Packing**

|           |           |            |           |
|-----------|-----------|------------|-----------|
| Packaging | Box       | VPE length | 348.00 mm |
| VPE width | 138.00 mm | VPE height | 31.00 mm  |

**Important note**

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |  |  |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |  |  |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Gold-plated contact surfaces on request</li> <li>• Spacing between rows: see hole layout</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |  |  |

## S2L-SMT 3.50/34/90LF 3.2SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002637    | ETIM 9.0    | EC002637    |
| ETIM 10.0   | EC002637    | ECLASS 14.0 | 27-46-02-01 |
| ECLASS 15.0 | 27-46-02-01 |             |             |

## Dimensional drawing

