

**TS 27X12.5M/ST/F.ZN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

**General ordering data**

Version	Terminal rail, Terminal rails, Steel, galvanized, Width: 2000 mm, Height: 27 mm, Depth: 12.5 mm
Order No.	<a href="#">1802690000</a>
Type	TS 27X12.5M/ST/F.ZN
GTIN (EAN)	4032248257201
Qty.	10 M

**TS 27X12.5M/ST/F.ZN**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	12.5 mm	Depth (inches)	0.4921 inch
Height	27 mm	Height (inches)	1.063 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	770 g		

**Temperatures**

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Mounting rail**

Installation advice	Direct mounting		
Standards	DIN EN 60715		
Surface finish	galvanized		
Thickness	2.00 mm		
Basic material	Steel		
Length of the terminal rail	min.	0 mm	
	nominal	2000 mm	
	max.	2000 mm	
Slit length	9.00 mm		
Slit width	9.00 mm		
Pre-punched mounting rail	Yes		
Slit width			
Spacing of holes, centre-to-centre	100 mm		
Slit gap			
Slit length			

**Classifications**

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

**Drawings**

