

**TS 27X12.5M/ST/F.ZN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

**General ordering data**

Version	Terminal rail, Terminal rails, Steel, galvanized, Width: 2000 mm, Height: 27 mm, Depth: 12.5 mm
Order No.	<a href="#">1802690000</a>
Type	TS 27X12.5M/ST/F.ZN
GTIN (EAN)	4032248257201
Qty.	10 M

## TS 27X12.5M/ST/F.ZN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	12.5 mm	Depth (inches)	0.4921 inch
Height	27 mm	Height (inches)	1.063 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	770 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Mounting rail

Installation advice	Direct mounting	
Standards	DIN EN 60715	
Surface finish	galvanized	
Thickness	2.00 mm	
Basic material	Steel	
Length of the terminal rail	min.	0 mm
	nominal	2000 mm
	max.	2000 mm
Slit length	9.00 mm	
Slit width	9.00 mm	
Pre-punched mounting rail	Yes	
Slit width		
Spacing of holes, centre-to-centre	100 mm	
Slit gap		
Slit length		

### Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

