

**SAIBGS-P-4A-3.5/5-M8****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M8 round plug-in connectors are particularly suited to applications where space is limited. The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

**General ordering data**

Version	Field attachable connector, M8
Order No.	<a href="#">1803880000</a>
Type	SAIBGS-P-4A-3.5/5-M8
GTIN (EAN)	403224825986 1
Qty.	1 items

**SAIBGS-P-4A-3.5/5-M8**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E307231

**Dimensions and weights**

Net weight	9.27 g
------------	--------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

**Technical data customisable plug-in connectors**

Number of poles	4	Coding	none
Contact surface	Gold-plated	Type of connection	Screw connection
Housing main material	PA	Insulation resistance	108 Ω
Cable diameter, max.	5 mm	Cable diameter, min.	3.5 mm
Conductor cross-section, max.	0.5 mm <sup>2</sup>	Conductor cross-section, min.	0.14 mm <sup>2</sup>
Nominal voltage	60 V	Nominal current	4 A
Protection degree	IP67	Plugging cycles	≥ 50
Pollution severity	3	Gender of contact	Female
Shield connection	No	Threaded ring material	Diecast zinc
Temperature range of housing	-40 ... +85 °C		

**Classifications**

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		