



Similar to illustration

Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

General ordering data

Version	TM, Socket x 5 mm, PVC, Colour: Transparent, Conductor O.D.: 1.5 - 2.5 mm
Order No.	1798620000
Type	TM 201/15 V0
GTIN (EAN)	4032248243358
Qty.	1000 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	0.27 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	5 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	Transparent
Basic material	PVC	Recommended industries	Transportation, Machinery
Operating temperature range	-40...80 °C		

Conductor and cable markers

Conductor cross-section, max.	1.5 mm ²	Conductor cross-section, min.	0.25 mm ²
Conductor O.D., max.	2.5 mm	Conductor O.D., min.	1.5 mm
Conductor O.D.	1.5 - 2.5 mm	Cross-section for connected wire	0.25 - 1.5 mm ²

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		