

## ST 4000/L CB M12/4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Thanks to the ring cable lug connection system, which is a proven railway technology, our ST 4000® high-voltage terminals provide you with a modular system that is both globally recognised and easy to install in all four corners of the world.

The products have been tested and comply with the requirements set down in the professional standards EN 50155, EN 50124-1, EN 45545 and IEC 61373. Our products are continuously monitored and further developed.

### General ordering data

Version	Bolt-type screw terminals, Busbar, Rated cross-section:
Order No.	<a href="#">1809290000</a>
Type	ST 4000/L CB M12/4
GTIN (EAN)	4032248293711
Qty.	100 items
Delivery status	This article will no longer be available in the future.

**ST 4000/L CB M12/4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	4 mm	Depth (inches)	0.1575 inch
Net weight	66.76 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Copper - zinc	Colour	silver
----------------	---------------	--------	--------

**System specifications**

Version	Miscellaneous	Number of levels	1
Levels cross-connected internally	No	PE connection	No

**Additional technical data**

Explosion-tested version	No	Type of mounting	Direct mounting
--------------------------	----	------------------	-----------------

**Conductors for clamping (rated connection)**

Wire connection cross section, finely stranded, max.	150 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	10 mm <sup>2</sup>
--	---------------------	--	--------------------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-14-11-92
ECLASS 15.0	27-14-11-92		