

TS 27X12.5M/ST/F.ZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Terminal rail, Terminal rails, Steel, galvanized, Width: 2000 mm, Height: 27 mm, Depth: 12.5 mm
Order No.	1802690000
Type	TS 27X12.5M/ST/F.ZN
GTIN (EAN)	4032248257201
Qty.	10 M

TS 27X12.5M/ST/F.ZN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	12.5 mm	Depth (inches)	0.4921 inch
Height	27 mm	Height (inches)	1.063 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	875 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Mounting rail

Installation advice	Direct mounting		
Standards	DIN EN 60715		
Surface finish	galvanized		
Thickness	2.00 mm		
Basic material	Steel		
Length of the terminal rail	min.	0 mm	
	nominal	2000 mm	
	max.	2000 mm	
Slit length	9.00 mm		
Slit width	9.00 mm		
Pre-punched mounting rail	Yes		
Slit width			
Spacing of holes, centre-to-centre	100 mm		
Slit gap			
Slit length			

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

Drawings

