

WQB 240/2**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, Silver grey, 320 A, Number of poles: 2, Pitch in mm (P): 5.10, Insulated: Yes, Width: 63.3 mm
Order No.	1802790000
Type	WQB 240/2
GTIN (EAN)	4032248313730
Qty.	5 items

WQB 240/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	43.5 mm	Depth (inches)	1.7126 inch
Height	49.3 mm	Height (inches)	1.9409 inch
Width	63.3 mm	Width (inches)	2.4921 inch
Net weight	150.6 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	tinned copper	Colour	Silver grey
----------------	---------------	--------	-------------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Type of fixing	when screwed in	Installation advice	Feed-through (bushing)
Explosion-tested version	No	Type of mounting	when screwed in

Dimensions

Pitch in mm (P)	5.10 mm
-----------------	---------

General

Number of poles	2	Installation advice	Feed-through (bushing)
-----------------	---	---------------------	------------------------

Rating data

Nominal current	320 A
-----------------	-------

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		