

WQB 240/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, Silver grey, 320 A, Number of poles: 3, Pitch in mm (P): 5.10, Insulated: Yes, Width: 99.3 mm
Order No.	1802800000
Type	WQB 240/3
GTIN (EAN)	4032248313747
Qty.	5 items

WQB 240/3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	43.5 mm	Depth (inches)	1.7126 inch
Height	49.3 mm	Height (inches)	1.9409 inch
Width	99.3 mm	Width (inches)	3.9094 inch
Net weight	208.56 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material tinned copper Colour Silver grey

System specifications

Version Cross-connector

Additional technical data

Type of fixing	when screwed in	Installation advice	Feed-through (bushing)
Explosion-tested version	No	Type of mounting	when screwed in

Dimensions

Pitch in mm (P) 5.10 mm

General

Number of poles 3 Installation advice Feed-through (bushing)

Rating data

Nominal current 320 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		