

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Silver grey, 320 A, Number of poles: 3, Pitch in mm (P): 5.10, Insulated: Yes, Width: 99.3 mm
Order No.	<a href="#">1802800000</a>
Type	WQB 240/3
GTIN (EAN)	4032248313747
Qty.	5 items

**Technical data****Approvals**

RoHS	Conform
------	---------

**Dimensions and weights**

Depth	43.5 mm	Depth (inches)	1.7126 inch
Height	49.3 mm	Height (inches)	1.9409 inch
Width	99.3 mm	Width (inches)	3.9094 inch
Net weight	208.56 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	tinned copper	Colour	Silver grey
----------------	---------------	--------	-------------

**System specifications**

Version	Cross-connector
---------	-----------------

**Additional technical data**

Type of fixing	when screwed in	Installation advice	Feed-through (bushing)
Explosion-tested version	No	Type of mounting	when screwed in

**Dimensions**

Pitch in mm (P)	5.10 mm
-----------------	---------

**General**

Number of poles	3	Installation advice	Feed-through (bushing)
-----------------	---	---------------------	------------------------

**Rating data**

Nominal current	320 A
-----------------	-------

**Classifications**

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		