Data sheet

SAISWI-P-4A-4/5.1-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.
Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.
The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

General ordering data

Version	Field attachable connector, M12
Order No.	1812870000
Type	SAISWI-P-4A-4/5.1-M12
GTIN (EAN)	4032248296422
Qty.	1 items

Data sheet

SAISWI-P-4A-4/5.1-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Dimensions and weights

Diameter	15 mm	Net weight	20 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data customisable plug-in connectors

Number of poles	4	Coding	A-coded
Contact surface	tinned	LED	No
Type of connection	Insulation displacement connection	Housing main material	CuZn
Cable diameter, max.	5.1 mm	Cable diameter, min.	4 mm
Conductor cross-section, max.	0.5 mm²	Conductor cross-section, min.	0.25 mm²
Nominal voltage	32 V	Nominal current	4 A
Protection degree	IP67	Plugging cycles	≥ 50
Pollution severity	3	Gender of contact	Male
Shield connection	No	Threaded ring material	Diecast zinc
Temperature range of housing	-25...+85 °C		

General Info

Number of poles	4	Connection 1	M12
Connection 2	IDC	Description of article	SAISW IDC / SAIBW IDC
UL 94 flammability rating	V-0	Housing main material	CuZn
Connection thread	M12	Contact surface	tinned
Wire connection cross section, finely stranded, min.	0.14 mm²	Wire connection cross-section, finely stranded, max.	0.34 mm²
Protection degree	IP67	Plugging cycles	≥ 50

Standards

Connector standard	IEC 61076-2-101

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

SAISWI-P-4A-4/5.1-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Pole scheme

