



Similar to illustration

Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

#### General ordering data

Version	TM, Socket x 9 mm, PVC, Colour: Transparent, Conductor O.D.: 6 - 10 mm
Order No.	<a href="#">1806360000</a>
Type	TM 204/20 V0
GTIN (EAN)	4032248275878
Qty.	500 items

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	9 mm	Depth (inches)	0.3543 inch
Height	20 mm	Height (inches)	0.7874 inch
Width	9 mm	Width (inches)	0.3543 inch
Net weight	0.72 g		

## Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Type of printing	neutral	Width	9 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	Transparent
Basic material	PVC	Recommended industries	Transportation, Machinery
Operating temperature range	-40...80 °C		

## Conductor and cable markers

Conductor cross-section, max.	16 mm <sup>2</sup>	Conductor cross-section, min.	6 mm <sup>2</sup>
Conductor O.D., max.	10 mm	Conductor O.D., min.	6 mm
Conductor O.D.	6 - 10 mm	Cross-section for connected wire	6 - 16 mm <sup>2</sup>

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		