Data sheet

SAIE-M12S-5-0.5U-FP-PG9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, M12, pin, straight, Mounting thread: PG 9, Number of poles: 5, Strand / cable length: 0.5 m, Front mounting
Order No.	1814900000
Type	SAIE-M12S-5-0.5U-FP-PG9
GTIN (EAN)	4032248303137
Qty.	1 items

SAIE-M12S-5-0.5U-FP-PG9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

Dimensions and weights

Net weight	34 g

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical specifications for cable

PE function	No	Core cross-section	0.34 mm²
Strand / cable length	0.5 m	Colour coding	brown, white, blue, black, grey
Number of poles	5		

Technical data customisable plug-in connectors

Number of poles	5	Coding	A-coded
Contact surface	Gold-plated	Housing main material	Brass, nickel-plated
Nominal voltage	60 V	Protection degree	IP67, when screwed in
Plugging cycles	≥ 100	Cable gland	PG 9

Standards

Connector standard	IEC 61076-2-101

General data

Number of poles	5
Coding	A-coded
Connection thread	M12
Contact surface	Gold-plated
Tightening torque	1 Nm
Core cross-section	0.34 mm²
Housing main material	Brass, nickel-plated
Type of mounting	Front mounting
Nominal voltage	60 V
Protection degree	IP67, when screwed in
Plugging cycles	≥ 100
Cable gland	PG 9
Basic material	PVC
Rated voltage	250 V (4-pole) / 125 V (5-pole) / 60 V (8-pole)
Connection 1	M12
Connection 2	Flying wires
Strand / cable length	0.5 m

SAIE-M12S-5-0.5U-FP-PG9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Mounting thread	PG 9	
Mounting torque range	2 Nm	
Mounting torque	max.	2 Nm
Conductor O.D.	-	

Classifications

ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		


SAIE-M12S-5-0.5U-FP-PG9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Wiring diagram



Pole scheme

