

TS 35X7.5 2M/ST/ZN O.SH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm
Order No.	1815020000
Type	TS 35X7.5 2M/ST/ZN O.SH
GTIN (EAN)	4032248305148
Qty.	40 M

TS 35X7.5 2M/ST/ZN O.SH

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	342 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Mounting rail

Standards	In accordance with DIN EN 60715	Surface finish	galvanic zinc plated and passivated
Thickness	1.00 mm	Basic material	Steel
Slit length	0.00 mm	Short-time withstand current per second according to IEC 60947-7-2	1.92 kA
Slit width	0.00 mm	Pre-punched mounting rail	No
Short circuit strength corresponds to E-Cu wire	16.00 mm ²	Spacing of holes, centre-to-centre	0 mm

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

Data sheet

TS 35X7.5 2M/ST/ZN O.SH

Drawings

