



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The 7/8" round plug-in connectors can transmit large amount of power.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

#### General ordering data

|            |                                  |
|------------|----------------------------------|
| Version    | Field attachable connector, 7/8" |
| Order No.  | <a href="#">1808840000</a>       |
| Type       | SAIS-4/9-7/8                     |
| GTIN (EAN) | 4032248281374                    |
| Qty.       | 1 items                          |

Technical data

Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate No. (cURus) | E307231                    |

Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 46.64 g |
|------------|---------|

Temperatures

|                     |                       |                |
|---------------------|-----------------------|----------------|
| Storage temperature | Operating temperature | -20 °C...85 °C |
|---------------------|-----------------------|----------------|

Environmental Product Compliance

|                                      |  |
|--------------------------------------|--|
| RoHS Compliance Status               | Compliant with exemption                       |
| RoHS Exemption (if applicable/known) | 6c   |
| REACH SVHC                           | Lead 7439-92-1, Imidazolidine-2-thione 96-45-7 |
| SCIP                                 | 10f6f563-34ca-4ce4-9e59-cf656b2f4d8b           |

Technical data customisable plug-in connectors

|                                |                     |                                |                                    |
|--------------------------------|---------------------|--------------------------------|------------------------------------|
| Number of poles                | 4                   | Coding                         | none                               |
| Contact surface                | Gold-plated         | Type of connection             | Screw connection                   |
| Housing main material          | PBT                 | Insulation resistance          | 108 Ω                              |
| Cable diameter, max.           | 8 mm                | Cable diameter, min.           | 6 mm                               |
| Contact material               | CuZn                | Conductor cross-section, max.  | 1.5 mm <sup>2</sup>                |
| Conductor cross-section, min.  | 0.5 mm <sup>2</sup> | Nominal voltage                | 300 V                              |
| Nominal current                | 9 A                 | Protection degree              | IP67                               |
| Plugging cycles                | ≥ 50                | Pollution severity             | 3                                  |
| Cable gland                    | PG 9                | Rated current                  | 9 A (4- and 5-pole), 12 A (3-pole) |
| Gender of contact              | Male                | Shield connection              | No                                 |
| Threaded ring material         | Diecast zinc        | Temperature range of housing   | -40 ... +85 °C                     |
| Connection cross-section, max. | 1.5 mm <sup>2</sup> | Connection cross-section, min. | 0.14 mm <sup>2</sup>               |

General data

|                               |                     |                               |                                    |
|-------------------------------|---------------------|-------------------------------|------------------------------------|
| Number of poles               | 4                   | Coding                        | none                               |
| Connection thread             | 7/8"                | Contact surface               | Gold-plated                        |
| Type of connection            | Screw connection    | Housing main material         | PBT                                |
| Insulation resistance         | 108 Ω               | Cable diameter, max.          | 8 mm                               |
| Cable diameter, min.          | 6 mm                | Contact material              | CuZn                               |
| Conductor cross-section, max. | 1.5 mm <sup>2</sup> | Conductor cross-section, min. | 0.5 mm <sup>2</sup>                |
| Nominal voltage               | 300 V               | Nominal current               | 9 A                                |
| Protection degree             | IP67                | Plugging cycles               | ≥ 50                               |
| Pollution severity            | 3                   | Cable gland                   | PG 9                               |
| Rated voltage                 | 300 V               | Rated current                 | 9 A (4- and 5-pole), 12 A (3-pole) |
| Connection 1                  | 7/8"                | Connection 2                  | Screw                              |
| Rated impulse voltage         | 4000 V              | Shield connection             | No                                 |

## Technical data

|                    |       |                              |                 |
|--------------------|-------|------------------------------|-----------------|
| Rated voltage (UL) | 600 V | Temperature range of housing | -40 ... +85 ° C |
| Conductor O.D.     | -     |                              |                 |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002635    | ETIM 9.0    | EC002635    |
| ETIM 10.0   | EC002635    | ECLASS 14.0 | 27-44-01-16 |
| ECLASS 15.0 | 27-44-01-16 |             |             |

**Drawings**

