Data sheet

ST 4000/L M M10

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Thanks to the ring cable lug connection system, which is a proven railway technology, our ST 4000® high-voltage terminals provide you with a modular system that is both globally recognised and easy to install in all four corners of the world.
The products have been tested and comply with the requirements set down in the professional standards EN 50155, EN 50124-1, EN 45545 and IEC 61373. Our products are continuously monitored and further developed.

General ordering data

Version	Bolt-type screw terminals, Marking tags, Rated cross-section:
Order No.	1809450000
Type	ST 4000/L M M10
GTIN (EAN)	4032248293889
Qty.	150 items
Delivery status	Discontinued

ST 4000/L M M10

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Net weight	10.37 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Colour	Brass coloured

System specifications

Number of levels	1	Levels cross-connected internally	No
PE connection	No		

Additional technical data

Explosion-tested version	No	Type of mounting	Direct mounting

Conductors for clamping (rated connection)

Wire connection cross section, finely stranded, max.	150 mm²	Wire connection cross section, finely stranded, min.	10 mm²

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		