

**KSW 2.5 EL WS 50M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



KSW marking strips are used to identify multi-pole PCB plug-in connectors. Users can print them individually without being confined to a certain pitch.

- Smudge-proof labelling
- Strips 2.5 mm and 4 mm wide
- Simply stick on - finished
- Optimum adhesion
- PVC-free

**General ordering data**

|            |   |
|------------|---|
| Version    | KSW, Terminal marker, 2.5 x , Pitch in mm (P):<br>2.50 Weidmueller, white |
| Order No.  | <a href="#">1812660000</a>  |
| Type       | KSW 2.5 EL WS 50M   |
| GTIN (EAN) | 4032248296064   |
| Qty.       | 50 M  |

**KSW 2.5 EL WS 50M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Height     | 2.5 mm   | Height (inches) | 0.0984 inch |
| Length     | 50000 mm | Length (inches) | 1968.5 inch |
| Net weight | 15.83 g  |                 |             |

**Temperatures**

Operating temperature range 150 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

|                                   |                     |                             |                         |
|-----------------------------------|---------------------|-----------------------------|-------------------------|
| Adhesive                          | Acrylate            | Orientation of print        | horizontal and vertical |
| Number per sheet                  | 20                  | Type of printing            | neutral                 |
| Operating temperature range, max. | 150 °C              | Colour                      | white                   |
| Halogen                           | No                  | Length                      | 50000 mm                |
| Basic material                    | Polyester, PVC-free | Printed characters          | without                 |
| compatible printer                |                     | Operating temperature range | 150 °C                  |
| Application/manufacturer          | Weidmueller         | Imprint                     | Neutral                 |

**Device markers**

Halogen No

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

**Drawings**

