

SAIB-M23-19P-ST-60M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

The M23 cables offer: high mating frequency, high current carrying capacity and high-density contacts coupled with minimal dimensions.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

| | |
|------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version | Sensor/actuator line, One end without connector, M23, Number of poles: 19, 60 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No. | 1818186000 |
| Type | SAIB-M23-19P-ST-60M |
| GTIN (EAN) | 4050118042399 |
| Qty. | 1 items |

SAIB-M23-19P-ST-60M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E486077

Dimensions and weights

Net weight 7360 g

Environmental Product Compliance

RoHS Compliance Status Compliant

REACH SVHC Lead 7439-92-1

SCIP ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical specifications for cable

| | | | |
|------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------|-----------------------|
| Cable length | 60 m | Sheathing colour | black |
| Suitable for cable carriers | Yes | Shielded | No |
| Halogen | No | Insulation | TPM |
| Bending radius, min., moving | 10 x cable diameter | Bending cycles | 2 Mio |
| Wire cross section (Print/Online) | 3 x 0.75 mm ² + 16 x 0.34 mm ² | Sheath material | PUR |
| Outer cladding in accordance with UL AWM style | 21198 (80 °C / 300 V) | Core in accordance with UL AWM style | 10493 (80 °C / 300 V) |
| Irradiation crosslinked | No | Welding spark resistance | No |
| Colour coding | violet, red, grey, red / blue, green, blue, grey / pink, white / green, white / yellow, white / grey, black, Green/yellow, Yellow / brown, brown / green, white, yellow, pink, grey / brown, brown | Torsion resistance | 0 °/m |
| Temperature range, stationary | -50...80 °C | Resistant to welding beads | No |
| Temperature range, moving | -25...80 °C | Number of poles | 19 |
| Outside diameter | 9.1 mm ± 0.3 mm | | |

General technical data

| | |
|-------------------------|-------------------------|
| Connection thread | M23 |
| Contact surface | Gold-plated |
| LED | No |
| Version | Female socket, straight |
| Housing main material | PUR |
| Insulation resistance | 1012 Ω |
| Nominal voltage | 120 V |
| Nominal current | 8 A |
| Protection degree | IP67 |
| Plugging cycles | ≥ 50 |
| Pollution severity | 2 |
| jumpered | No |
| Connection side version | Connection side 1 |

SAIB-M23-19P-ST-60M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | |
|------------------------------|-------------------------------------|--------------|
| | Connection thread | M23 |
| | Type of contact | Socket |
| | Type of thread | Inner thread |
| | Outlet direction | straight |
| Connection side version 1 | M23, Socket, Inner thread, straight | |
| Threaded ring material | Diecast zinc | |
| Temperature range of housing | -25...+80 °C | |
| Tightening torque | M23: 2.5 Nm | |

Electrical properties

| | | | |
|-----------------------|--------|-----------------|-------|
| Insulation resistance | 1012 Ω | Nominal voltage | 120 V |
|-----------------------|--------|-----------------|-------|

General standards

| | |
|-------------------------|---------|
| Certificate No. (cURus) | E486077 |
|-------------------------|---------|

Plug, left

| | |
|-----------|-----------------------------------------------------|
| Plug left | IP67, female contact, straight, Plastic, unshielded |
|-----------|-----------------------------------------------------|

Plug, right

| | |
|------------|--------------------|
| Plug right | free conductor end |
|------------|--------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ETIM 10.0 | EC001855 | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 | | |

SAIB-M23-19P-ST-60M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Straight socket

Pole scheme



Socket

Wiring diagram



The ideal tool: Screwty® with torque function

Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

