

## HDC HB 24 TEK TOS1XM50G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

### General ordering data

|            |  |
|------------|--|
| Version    | HDC enclosures, Installation size: 8, Protection degree: IP66, IP68, in plugged condition, Plug housing, Clamping yoke connection, high, Size of cable entries: M 50 |
| Order No.  | <a href="#">1827170000</a>   |
| Type       | HDC HB 24 TEK TOS1XM50G  |
| GTIN (EAN) | 4032248332328  |
| Qty.       | 1 items  |

**HDC HB 24 TEK TOS1XM50G**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 120 mm | Height (inches) | 4.7244 inch |
| Width      | 58 mm  | Width (inches)  | 2.2835 inch |
| Net weight | 733 g  |                 |             |

**Temperatures**

Limit temperature -50 °C ... 125 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

|                     |                     |                         |
|---------------------|---------------------|-------------------------|
| Chemical resistance | Substance           | Acetone                 |
|                     | Chemical resistance | Resistant               |
|                     | Substance           | Diesel oil              |
|                     | Chemical resistance | Unstable                |
|                     | Substance           | Ethyl alcohol           |
|                     | Chemical resistance | Resistant               |
|                     | Substance           | Transmission oil        |
|                     | Chemical resistance | Conditionally resistant |
|                     | Substance           | Hydraulic oil           |
|                     | Chemical resistance | Conditionally resistant |
|                     | Substance           | Petroleum benzine       |
|                     | Chemical resistance | Unstable                |
|                     | Substance           | Sweat                   |
|                     | Chemical resistance | Conditionally resistant |
|                     | Substance           | Premium gasoline        |
|                     | Chemical resistance | Unstable                |
|                     | Substance           | Water                   |
|                     | Chemical resistance | Resistant               |
|                     | Substance           | UV                      |
|                     | Chemical resistance | Resistant               |
| Substance           | Ozone               |                         |
| Chemical resistance | Resistant           |                         |

**Dimensions**

|                     |           |                      |        |
|---------------------|-----------|----------------------|--------|
| Cable entry         | w. thread | Total length housing | 184 mm |
| Height of housing B | 120 mm    |                      |        |

**General data**

|                |                |                   |                                  |
|----------------|----------------|-------------------|----------------------------------|
| Surface finish | Powder coating | Protection degree | IP66, IP68, in plugged condition |
|----------------|----------------|-------------------|----------------------------------|

## HDC HB 24 TEK TOS1XM50G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Version

|                              |                          |                                |                          |
|------------------------------|--------------------------|--------------------------------|--------------------------|
| Size of cable entries        | M 50                     | Top part/bottom part/lid       | upper part               |
| Cover                        | without cover            | Tightening torque              | 6.5 Nm                   |
| Number of cable entry on top | 1                        | Number of cable entry sideways | 0                        |
| Design of housing            | Plug housing             | Design of locking system       | Clamping yoke connection |
| Design                       | high                     | Installation size              | 8                        |
| Cable entry                  | w. thread                | Type                           | Plug                     |
| Clamp version                | Clamping yoke connection | Sealing                        | no sealing               |
| Internal thread              | M 50                     | Colour (RAL)                   | RAL 9011                 |
| BG                           | 8                        | Suitable for ModuPlug®         | Yes                      |

### Classifications


|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000437    | ETIM 9.0    | EC000437    |
| ETIM 10.0   | EC000437    | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 |             |             |

**HDC HB 24 TEK TOS1XM50G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



## HDC HB 24 TEK TOS1XM50G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Socket wrench sets



Allen key made from fully hardened, high-alloy chromium-vanadium-steel, acc. to DIN ISO 2936 L (DIN 911), high-quality refined surface.

### General ordering data

|            |                            |               |  |
|------------|----------------------------|---------------|--|
| Type       | SK WSD-S 1,5-10,0          | Version       |  |
| Order No.  | <a href="#">9008850000</a> | Mounting tool |  |
| GTIN (EAN) | 4032248266609              |               |  |
| Qty.       | 1 ST                       |               |  |

### Screws



We offer a variety of accessories, including screws, that fit to the heavy-duty connectors.

### General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | HDC IP68 SCREW SET         | Version  |  |
| Order No.  | <a href="#">2555340000</a> | Heavy-duty connectors, Accessories, Set of fixings |  |
| GTIN (EAN) | 4050118571332              |  |  |
| Qty.       | 10 ST                      |  |  |

### IP68 version



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications. The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure. Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | VG M50 - MS 68             | Version  |  |
| Order No.  | <a href="#">1772260000</a> | VG MS (standard brass cable gland), Cable glands, straight, M 50, 9 mm, OD min. 22 - OD max. 32 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Brass, nickel-plated |  |
| GTIN (EAN) | 4032248129911              |  |  |
| Qty.       | 5 ST                       |  |  |