

**HDC CM 2 FS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The CM high-current module is a double module and takes up two slots in the ConCept module frame. The wire is attached with a screw connection. The module can be used simply as a two-pole power module or as a combination of a one-pole power module and a one-pole PE module. The modules feature an integrated module release aid. No additional removal tool is needed.

**General ordering data**

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	<a href="#">1828400000</a>
Type	HDC CM 2 FS
GTIN (EAN)	4032248334629
Qty.	5 items

## HDC CM 2 FS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	45 mm	Height (inches)	1.7716 inch
Width	22.8 mm	Width (inches)	0.8976 inch
Net weight	35.73 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	e98b2b24-ba23-41bf-8d19-0dda3647412f

## ConCept Pneumatic module

UL 94 flammability rating	V-0	Colour	black
---------------------------	-----	--------	-------

## Dimensions

Width	22.8 mm	Total length base	34 mm
Height of socket	45 mm		

## General data

Number of poles	2	Type of connection	Screw connection
UL 94 flammability rating	V-0	Volume resistance	≤1 mΩ
Colour	black	Insulation resistance	1012 Ω
Insulating material	Polyamide with fibre optic	Type	Female
Surge voltage category	III	Pollution severity	3
Basic material	Polyamide, glass fibre-reinforced	Series	ConCept module
Rated voltage (DIN EN 61984)	1000 V	Rated impulse voltage (DIN EN 61984)	8 kV
Rated current (DIN EN 61984)	82 A	Free from halogens	false
Low smoke acc. DIN EN 45545-2	Yes		

## Connection data PE

Connection type PE	Screw connection via module frame
--------------------	-----------------------------------

## Version

Wire connection cross section AWG, max.	AWG 4	Stripping length, rated connection	16 mm
Type of connection	Screw connection	Volume resistance	≤1 mΩ

**HDC CM 2 FS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

Wire connection cross section AWG, min.	AWG 8	Conductor cross-section, max.	25 mm <sup>2</sup>
Conductor cross-section, min.	10 mm <sup>2</sup>	Basic material	Polyamide, glass fibre-reinforced

**Classifications**

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		