


**ZDU 16 OR****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

|            |  |
|------------|--|
| Version    | Feed-through terminal, Tension-clamp connection, 16 mm <sup>2</sup> , 1000 V, 76 A, orange |
| Order No.  | <a href="#">1830680000</a>   |
| Type       | ZDU 16 OR  |
| GTIN (EAN) | 4032248706570  |
| Qty.       | 25 items   |

## ZDU 16 OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



|                           |                            |
|---------------------------|----------------------------|
| ROHS                      | Conform                    |
| UL File Number Search     | <a href="#">UL Website</a> |
| Certificate No. (cURus)   | E60693                     |
| Certificate No. (cURusEX) | E184763                    |

## Dimensions and weights

|                          |             |                |             |
|--------------------------|-------------|----------------|-------------|
| Depth                    | 50.5 mm     | Depth (inches) | 1.9882 inch |
| Depth including DIN rail | 51.5 mm     | Height         | 82.5 mm     |
| Height (inches)          | 3.248 inch  | Width          | 12.1 mm     |
| Width (inches)           | 0.4764 inch | Net weight     | 33.9 g      |

## Temperatures

|                                  |                |                                  |                |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -50 °C...75 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 120 °C         |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Basic material            | Wemid | Colour | orange |
| UL 94 flammability rating | V-0   |        |        |

## Rating data IECEx/ATEX

|                                |                    |                                 |                    |
|--------------------------------|--------------------|---------------------------------|--------------------|
| Certificate No. (ATEX)         | DEMKO15ATEX1467U   | Certificate No. (IECEX)         | IECEXULD15.0008U   |
| Max. voltage (ATEX)            | 690 V              | Current (ATEX)                  | 68 A               |
| Wire cross section max. (ATEX) | 25 mm <sup>2</sup> | Max. voltage (IECEX)            | 690 V              |
| Current (IECEX)                | 68 A               | Wire cross section max. (IECEX) | 25 mm <sup>2</sup> |
| Marking EN 60079-7             | Ex eb II C Gb      | Ex 2014/34/EU label             | II 2 G D           |

## System specifications

|                                     |  |                               |     |
|-------------------------------------|--|-------------------------------|-----|
| Version                             | Tension-clamp connection, for plug-in cross-connector, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 1  | Number of levels              | 1   |
| Number of clamping points per level | 2  | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No   | PE connection                 | No  |
| Mounting rail                       | TS 35  |                               |     |

## ZDU 16 OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Additional technical data

|                          |       |                             |         |
|--------------------------|-------|-----------------------------|---------|
| Open sides               | right | Number of similar terminals | 1       |
| Explosion-tested version | Yes   | Type of mounting            | Snap-on |

## CSA rating data

|                               |        |                       |                |
|-------------------------------|--------|-----------------------|----------------|
| Wire cross section max. (CSA) | 4 AWG  | Voltage size C (CSA)  | 600 V          |
| Current size C (CSA)          | 65 A   | Certificate No. (CSA) | 200039-1152892 |
| Voltage size B (CSA)          | 600 V  | Current size B (CSA)  | 65 A           |
| Wire cross section min. (CSA) | 14 AWG |                       |                |

## Conductors for clamping (additional connection)

Connection type, additional connection Tension-clamp connection

## Conductors for clamping (rated connection)

|   |                          |   |                     |
|---|--------------------------|---|---------------------|
| Gauge to IEC 60947-1  | A7                       | Wire connection cross section AWG, max.   | AWG 4               |
| Connection direction  | top                      | Stripping length  | 18 mm               |
| Type of connection  | Tension-clamp connection | Number of connections   | 2                   |
| Clamping range, max.  | 25 mm <sup>2</sup>       | Clamping range, min.  | 1.5 mm <sup>2</sup> |
| Blade size  | 1.0 x 5.5 mm             | Wire connection cross section AWG, min.   | AWG 14              |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 16 mm <sup>2</sup>       | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 1.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 16 mm <sup>2</sup>       | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 1.5 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, max.                                    | 16 mm <sup>2</sup>       | Wire connection cross section, finely stranded, min.                                    | 1.5 mm <sup>2</sup> |
| Connection cross-section, stranded, max.  | 25 mm <sup>2</sup>       | Connection cross-section, stranded, min.  | 1.5 mm <sup>2</sup> |
| Wire connection cross-section, solid core, max.   | 16 mm <sup>2</sup>       | Wire connection cross-section, solid core, min.   | 1.5 mm <sup>2</sup> |
| Connection cross-section, finely stranded, min.   | 1.5 mm <sup>2</sup>      |   |                     |

## Dimensions

TS 35 offset 42 mm

## General

|   |               |   |        |
|---|---------------|---|--------|
| Wire connection cross section AWG, max. | AWG 4         | Wire connection cross section AWG, min. | AWG 14 |
| Standards                               | IEC 60947-7-1 | Mounting rail                           | TS 35  |

## Rating data

|  |                    |                                 |               |
|--|--------------------|---------------------------------|---------------|
| Rated cross-section                          | 16 mm <sup>2</sup> | Rated voltage                   | 1000 V        |
| Rated DC voltage                             | 1000 V             | Nominal current                 | 76 A          |
| Current at maximum wires                     | 98 A               | Standards                       | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 0.42 mΩ            | Rated impulse withstand voltage | 8 kV          |
| Power loss in accordance with IEC 60947-7-x  | 2.43 W             | Pollution severity              | 3             |

## Technical data

### UL rating data

|                         |        |
|-------------------------|--------|
| Certificate No. (cURus) | E60693 |
|-------------------------|--------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ETIM 10.0   | EC000897    | ECLASS 14.0 | 27-25-01-01 |
| ECLASS 15.0 | 27-25-01-01 |             |             |

**Drawings**

