

QVAR 1**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	I-Series, Accessories, Cross-connect adapter, dark beige, 40 mm
Order No.	1836370000
Type	QVAR 1
GTIN (EAN)	4032248380510
Qty.	25 items

QVAR 1

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	6.1 mm	Depth (inches)	0.2402 inch
Height	99 mm	Height (inches)	3.8976 inch
Width	40 mm	Width (inches)	1.5748 inch
Net weight	10.6 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	for cross-connection link	Mounting rail	TS 35
---------	---------------------------	---------------	-------

Additional technical data

Type of fixing	Plugged	Explosion-tested version	No
----------------	---------	--------------------------	----

Dimensions

Pitch in mm (P)	6.10 mm
-----------------	---------

General

Number of poles	2	Mounting rail	TS 35
-----------------	---	---------------	-------

Rating data

Nominal current	24 A
-----------------	------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		