

QVAR 1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	I-Series, Accessories, Cross-connect adapter, dark beige, 40 mm
Order No.	1836370000
Type	QVAR 1
GTIN (EAN)	4032248380510
Qty.	25 items

QVAR 1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	6.1 mm	Depth (inches)	0.2402 inch
Height	99 mm	Height (inches)	3.8976 inch
Width	40 mm	Width (inches)	1.5748 inch
Net weight	10.6 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	for cross-connection link	Mounting rail	TS 35
---------	---------------------------	---------------	-------

Additional technical data

Type of fixing	Plugged	Explosion-tested version	No
----------------	---------	--------------------------	----

Dimensions

Pitch in mm (P)	6.10 mm
-----------------	---------

General

Number of poles	2	Mounting rail	TS 35
-----------------	---	---------------	-------

Rating data

Nominal current	24 A
-----------------	------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		