

**HDC CM 2 MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The CM high-current module is a double module and takes up two slots in the ConCept module frame. The wire is attached with a screw connection. The module can be used simply as a two-pole power module or as a combination of a one-pole power module and a one-pole PE module. The modules feature an integrated module release aid. No additional removal tool is needed.

**General ordering data**

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	<a href="#">1828380000</a>
Type	HDC CM 2 MS
GTIN (EAN)	4032248334100
Qty.	5 items

## HDC CM 2 MS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	47.8 mm	Height (inches)	1.8819 inch
Width	22.8 mm	Width (inches)	0.8976 inch
Net weight	44 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

## ConCept Pneumatic module

UL 94 flammability rating	V-0	Colour	black
---------------------------	-----	--------	-------

## Dimensions

Width	22.8 mm	Total length base	34 mm
Height of plug	47.8 mm		

## General data

Number of poles	2	Tightening torque	1.2 Nm
Type of connection	Screw connection	UL 94 flammability rating	V-0
Volume resistance	≤1 mΩ	Colour	black
Insulation resistance	1012 Ω	Insulating material	Polyamide with fibre optic
Type	Pin	Surge voltage category	III
Pollution severity	3	Basic material	Polyamide, glass fibre-reinforced
Series	ConCept module	Rated voltage (DIN EN 61984)	1000 V
Rated impulse voltage (DIN EN 61984)	8 kV	Rated current (DIN EN 61984)	82 A
Free from halogens	false	Low smoke acc. DIN EN 45545-2	Yes

## Connection data PE

Connection type PE	Screw connection via module frame
--------------------	-----------------------------------

## Version

Wire connection cross section AWG, max.	AWG 4	Stripping length, rated connection	16 mm
Type of connection	Screw connection	Volume resistance	≤1 mΩ

**HDC CM 2 MS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

Wire connection cross section AWG, min.	AWG 8	Conductor cross-section, max.	25 mm <sup>2</sup>
Conductor cross-section, min.	10 mm <sup>2</sup>	Basic material	Polyamide, glass fibre-reinforced

**Classifications**

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		