

HDC CM 2 FS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The CM high-current module is a double module and takes up two slots in the ConCept module frame. The wire is attached with a screw connection. The module can be used simply as a two-pole power module or as a combination of a one-pole power module and a one-pole PE module. The modules feature an integrated module release aid. No additional removal tool is needed.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1828400000
Type	HDC CM 2 FS
GTIN (EAN)	4032248334629
Qty.	5 items

HDC CM 2 FS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	45 mm	Height (inches)	1.7716 inch
Width	22.8 mm	Width (inches)	0.8976 inch
Net weight	35.73 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

ConCept Pneumatic module

UL 94 flammability rating	V-0	Colour	black
---------------------------	-----	--------	-------

Dimensions

Width	22.8 mm	Total length base	34 mm
Height of socket	45 mm		

General data

Number of poles	2	Tightening torque	1.2 Nm
Type of connection	Screw connection	UL 94 flammability rating	V-0
Volume resistance	≤1 mΩ	Colour	black
Insulation resistance	1012 Ω	Insulating material	Polyamide with fibre optic
Type	Female	Surge voltage category	III
Pollution severity	3	Basic material	Polyamide, glass fibre-reinforced
Series	ConCept module	Rated voltage (DIN EN 61984)	1000 V
Rated impulse voltage (DIN EN 61984)	8 kV	Rated current (DIN EN 61984)	82 A
Free from halogens	false	Low smoke acc. DIN EN 45545-2	Yes

Connection data PE

Connection type PE	Screw connection via module frame
--------------------	-----------------------------------

Version

Wire connection cross section AWG, max.	AWG 4	Stripping length, rated connection	16 mm
Type of connection	Screw connection	Volume resistance	≤1 mΩ

HDC CM 2 FS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Wire connection cross section AWG, min.	AWG 8	Conductor cross-section, max.	25 mm ²
Conductor cross-section, min.	10 mm ²	Basic material	Polyamide, glass fibre-reinforced

Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		