
Data sheet

# SAIE-M12B-5-0.5U-M16

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

## General ordering data

| | |
|---|---|
| Version | Built-in plugs, M12, Female socket, straight, Mounting thread: M 16 x 1.5, Number of poles: 5, Strand / cable length: 0.5 m, Front mounting |
| Order No. | 1836910000 |
| Type | SAIE-M12B-5-0.5U-M16 |
| GTIN (EAN) | 4032248344901 |
| Qty. | 1 items |

# Data sheet

## SAIE-M12B-5-0.5U-M16

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E307231 |

### Dimensions and weights

| | |
|---|---|
| Net weight | 30 g |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 4060c755-8d0b-4d43-bdb3-4ffabe9d7497 |

### Technical specifications for cable

| | | | |
|---|---|---|---|
| PE function | No | Core cross-section | 0.34 mm² |
| Strand / cable length | 0.5 m | Colour coding | brown, white, blue, black, grey |
| Number of poles | 5 | | |

### Technical data customisable plug-in connectors

| | | | |
|---|---|---|---|
| Number of poles | 5 | Coding | A-coded |
| Contact surface | Gold-plated | Housing main material | Zinc diecast |
| Nominal voltage | 60 V | Nominal current | 4 A |
| Protection degree | IP67, when screwed in | Plugging cycles | ≥ 100 |
| Temperature range of housing | -30...+90 °C | | |

### Standards

| | |
|---|---|
| Connector standard | IEC 61076-2-101 |

### General data

| | |
|---|---|
| Number of poles | 5 |
| Coding | A-coded |
| Connection thread | M12 |
| Contact surface | Gold-plated |
| Tightening torque | 1 Nm |
| Core cross-section | 0.34 mm² |
| Housing main material | Zinc diecast |
| Type of mounting | Front mounting |
| Nominal voltage | 60 V |
| Nominal current | 4 A |
| Protection degree | IP67, when screwed in |
| Plugging cycles | ≥ 100 |
| Basic material | PVC |
| Rated voltage | 250 V (4-pole) / 125 V (5-pole) / 60 V (8-pole) |
| Connection 1 | M12 |

# SAIE-M12B-5-0.5U-M16

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

| | | | |
|---|---|---|---|
| Connection 2 | Flying wires | | |
| Strand / cable length | 0.5 m | | |
| Mounting thread | M 16 x 1.5 | | |
| Mounting torque range | 2 Nm | | |
| Mounting torque | max. | 2 Nm | |
| Temperature range of housing | -30...+90 °C | | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC003570 | ETIM 9.0 | EC003570 |
| ETIM 10.0 | EC003570 | ECLASS 14.0 | 27-44-01-03 |
| ECLASS 15.0 | 27-44-01-03 | | |


**SAIE-M12B-5-0.5U-M16**

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

# Drawings

## Wiring diagram




## Pole scheme



# SAIE-M12B-5-0.5U-M16

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

### General ordering data

| | | |
|---|---|---|
| Type | SKMU M16 MS | Version |
| Order No. | 1736990000 | SKMU MS (brass locknut), Locknut, M 16, 2.8 mm, Brass, nickel- |
| GTIN (EAN) | 4008190956462 | plated |
| Qty. | 100 ST | |