

**SAI-04L-VPFC-4A-M08L-PNP-05U03**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

The new slim M8 line from Weidmüller. This range of products is characterised by the marking options at all connection positions. Even the 4-way distributor with 8-pole M12 has adequately large markers at all M8 connection positions. Furthermore, this distributor is shorter than many conventional M8 designs.

- Very narrow, short and flat M8 distributor.
- The range is supplied with 4 to 12 M8 connection positions, 3 or 4 poles.
- Hybrid variants of the M8 are also possible on request.
- The M8 line is equipped with transverse holes.

**General ordering data**

|            |  |
|------------|--|
| Version    | Fixed cable version, M8, 30 V, , LED: Yes, LED initiator: Yes, Wiring type: PNP, 5 m |
| Order No.  | <a href="#">1849680000</a>   |
| Type       | SAI-04L-VPFC-4A-M08L-PNP-05U03   |
| GTIN (EAN) | 4032248376674  |
| Qty.       | 1 items  |

## SAI-04L-VPFC-4A-M08L-PNP-05U03

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 18.2 mm  | Depth (inches)  | 0.7165 inch |
| Height     | 92 mm    | Height (inches) | 3.622 inch  |
| Width      | 24 mm    | Width (inches)  | 0.9449 inch |
| Net weight | 385.44 g |                 |             |

## Temperatures

Operating temperature -25 - 80°C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## Connection data

Sheathing stripping length 100 mm Distributor outlet Fixed cable version

## Electrical data

|                                |      |   |       |
|--------------------------------|------|---|-------|
| Rated voltage, min.            | 10 V | Rated voltage, max.                     | 30 V  |
| Test voltage                   | 1 kV | Max. current-carrying capacity per slot | 2 A   |
| Total current                  | 6 A  | Current per signal                      | 1 A   |
| Electrical isolation available | No   | Insulation resistance                   | 109 Ω |

## General technical data

|                                     |       |                             |        |
|-------------------------------------|-------|-----------------------------|--------|
| Protection degree                   | IP68  | Number of poles             | 4      |
| Number of contact sockets           | 4     | Connection thread           | M8     |
| Pollution severity                  | 3     | Fire behaviour              | V-0    |
| LED                                 | Yes   | LED initiator               | Yes    |
| LED colour for indicating operation | green | LED colour for I/O function | yellow |

## Material data

|                         |                    |                          |                             |
|-------------------------|--------------------|--------------------------|-----------------------------|
| Material O-Ring         | FKM                | Housing main material    | PBT                         |
| Material of distributor | Plastic            | Housing colour           | black (similar to RAL 9005) |
| Screw socket            | Nickel-plated CuZn | Contact material         | CuZn                        |
| Contact surface         | Gold-plated        | Contact carrier material | PBT (UL 94 V0)              |

## Technical data cable

|                 |        |                  |       |
|-----------------|--------|------------------|-------|
| Number of poles | 4      | Sheathing colour | black |
| O.D.            | 7.4 mm | Shielded         | No    |

Creation date 24.02.2026 09:18:09 MEZ

Catalogue status / Drawings

**SAI-04L-VPFC-4A-M08L-PNP-05U03**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

|                             |         |                                   |   |
|-----------------------------|---------|-----------------------------------|---|
| Halogen                     | No      | Bending radius, min., moving      | 10 x cable diameter                                 |
| Bending cycles              | 1 mill. | Wire cross section (Print/Online) | 8 x 0.34 mm <sup>2</sup> + 2 x 0.75 mm <sup>2</sup> |
| Sheath material             | PUR     | Cable length                      | 5 m   |
| Suitable for cable carriers | Yes     |                                   |   |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002585    | ETIM 9.0    | EC002585    |
| ETIM 10.0   | EC002585    | ECLASS 14.0 | 27-44-01-08 |
| ECLASS 15.0 | 27-44-01-08 |             |             |

**SAI-04L-VPFC-4A-M08L-PNP-05U03**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

**Drawings**

www.weidmueller.com

**Dimensioned drawing**

**Wiring**



**Pole scheme**

