

THM WO 12/18 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 1.9 - 1.9 mm, 12 x 18 mm, white
Order No.	1856640000
Type	THM WO 12/18 WS
GTIN (EAN)	4032248399581
Qty.	1 items

THM WO 12/18 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	492 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive	
Material colour according to resistance code	9	
Type of printing	neutral	
Version	Self-adhesive	
Width	18 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	No	
Basic material	Polyester film	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Size of labelling field	12 x 9 mm	
Approval acc. to UL 969	Yes	
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Operating temperature range	-40...150 °C	
Number per roll	10000	

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	0.75 mm ²	Conductor O.D., max.	1.9 mm
Conductor O.D., min.	1.9 mm	Text field width	12 mm
Text field height	9 mm	Conductor O.D.	1.9 - 1.9 mm
Cross-section for connected wire	0.75 - 6 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

THM WO 12/18 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Accessories

www.weidmueller.com

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	2005070000	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		