

SAIL-VSC-M12W-1.5U

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Weidmüller can supply valve plugs as connecting lines with M8/M12 plugs and one end without connector. The status of the valve plug is shown by an LED. The valve plugs have a protective circuit. The Weidmüller range includes valve plugs of type A, B and C to DIN and industry standards. Protection class IP 67 is fulfilled when screwed in. The outlet direction is also a decisive factor, therefore Weidmüller offers different versions.

General ordering data

Version	Valve cable (assembled), 90°; plug - valve plug, Industrial design C (9.4 mm), M12 = A-coded, Cable length: 1.5 m, PUR, black
Order No.	1857720150
Type	SAIL-VSC-M12W-1.5U
GTIN (EAN)	4032248404117
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-11-29T00:00:00+01:00

SAIL-VSC-M12W-1.5U

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



RoHS Conform

Dimensions and weights

Net weight 62.48 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

Technical specifications for cable

Cable length	1.5 m
Suitable for cable carriers	Yes
Shielded	No
Insulation	PP
Bending radius, min., moving	10 x cable diameter
Bending cycles	2 Mio
Sheath material	PUR
Colour coding	brown, blue, Green/yellow
Temperature range, stationary	-50...80 °C
Temperature range, moving	-25...80 °C
Outside diameter	4.6 mm ± 0.2 mm

Sheathing colour	black
Core cross-section	0.5 mm ²
Halogen	No
Acceleration	5 m/s ²
Bending radius, min., stationary	5 x cable diameter
Speed	200 m/s
Welding spark resistance	No
Torsion resistance	0 °/m
Resistant to welding beads	No
Number of poles	3

General technical data

Coding	Industrial design C (9.4 mm), M12 = A-coded
Contact surface	tinned
Version	90° plug - valve plug
Nominal voltage	24 V
Protection degree	IP67, when screwed in

Connection thread	Miscellaneous
LED	Yes
Contact material	CuZn
Nominal current	4 A
All valve plugs are fitted with protective circuits	Zener diode
Tightening torque	Mounting screw M3: 0.4 Nm, M2.5 mounting screw: 0.3 Nm, M12: 0.8 - 1.2 Nm

Classifications

ETIM 8.0	EC001855
ETIM 10.0	EC001855
ECLASS 15.0	27-06-03-12





ETIM 9.0	EC001855
ECLASS 14.0	27-06-03-12

SAIL-VSC-M12W-1.5U

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Dimensioned drawing**Dimensioned drawing****Pole scheme****Pole scheme****Wiring diagram**