

**Q WDU10-2.5 SET**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Silver grey, 57 A, Number of poles: 2, Pitch in mm (P): 7.00, Insulated: No, Width: 6 mm
Order No.	<a href="#">1859620000</a>
Type	Q WDU10-2.5 SET
GTIN (EAN)	4032248413331
Qty.	10 items

## Q WDU10-2.5 SET

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	22.5 mm	Depth (inches)	0.8858 inch
Height	13.9 mm	Height (inches)	0.5472 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	5.63 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	tinned copper	Colour	Silver grey
----------------	---------------	--------	-------------

### System specifications

Version	For the terminals
---------	-------------------

### Additional technical data

Type of fixing	when screwed in	Installation advice	Feed-through (bushing), Direct mounting
Explosion-tested version	No		

### Dimensions

Pitch in mm (P)	7.00 mm
-----------------	---------

### General

Number of poles	2	Installation advice	Feed-through (bushing), Direct mounting
-----------------	---	---------------------	--

### Rating data

Rated voltage	400 V	Nominal current	57 A
---------------	-------	-----------------	------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		