

SFX 11/60 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



SlimFix X are halogen-free conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. SlimFix is an acknowledged and approved marker type in traffic engineering. The SF tool allows easy installation even in case of small markers.

- Halogen-free material
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SlimFix X, Conductor and cable markers, 7 - 40 mm, 60 x 11 mm, To customer specification
Order No.	1860140000
Type	SFX 11/60 MC SDR
GTIN (EAN)	4032248416578
Qty.	12 items

SFX 11/60 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	60 mm	Height (inches)	2.3622 inch
Width	11 mm	Width (inches)	0.4331 inch
Net weight	1.52 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	Cradle to gate 0.018 kg CO2 eq.

General data

Orientation of print	horizontal
Type of printing	To customer specification
Printing method	MC Laser, PrintJet ADVANCED
Version	Installation with cable ties
Width	11 mm
UL 94 flammability rating	V-2
Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C
Colour	To customer specification
Halogen	No
Basic material	Polyamide 66
Colour of printing	black, coloured
Printed characters	Requires M-Print PRO File
Advice label	Colour based on customer requirements (Please send M-Print PRO file)
Number of markers per packaging unit	Form of supply MultiCard
Size of labelling field	44 x 11 mm
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2
Number of markers per combination	1 MultiCard = Conductor and cable markers
Operating temperature range	-40...100 °C

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	16 mm ²	Conductor O.D., max.	40 mm
Conductor O.D., min.	7 mm	Conductor O.D.	7 - 40 mm
Cross-section for connected wire	16 - 500 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		