


SAIE-M12S-8-0.5U-M16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

| | |
|------------|---|
| Version | Built-in plugs, M12, pin, straight, Mounting thread: M 16 x 1.5, Number of poles: 8, Strand / cable length: 0.5 m, Front mounting |
| Order No. | 1861110000 |
| Type | SAIE-M12S-8-0.5U-M16 |
| GTIN (EAN) | 4032248419159 |
| Qty. | 1 items |

SAIE-M12S-8-0.5U-M16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E307231 |

Dimensions and weights

| | |
|------------|------|
| Net weight | 29 g |
|------------|------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | ebf89fc8-a87f-4691-b87a-dfb9921774b4 |

Technical specifications for cable

| | | | |
|-----------------------------------|---|-----------------------|----------------------|
| PE function | No | Core cross-section | 0.25 mm ² |
| Wire cross section (Print/Online) | 0.34 (4- and 5-pole)/ 0.25 (8-pole)/ 0.14 (12-pole) | Strand / cable length | 0.5 m |
| Colour coding | white, brown, green, yellow, grey, pink, blue, red | Number of poles | 8 |

Technical data customisable plug-in connectors

| | | | |
|-------------------|--|------------------------------|----------------------|
| Number of poles | 8 | Coding | A-coded |
| Contact surface | Gold-plated | Housing main material | Brass, nickel-plated |
| Nominal voltage | 30 V | Nominal current | 2 A |
| Protection degree | IP67, when screwed in | Plugging cycles | ≥ 100 |
| Rated current | 4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole) | Temperature range of housing | -30...+90 °C |

Standards

| | |
|--------------------|-----------------|
| Connector standard | IEC 61076-2-101 |
|--------------------|-----------------|

General data

| | |
|-----------------------|-----------------------|
| Number of poles | 8 |
| Coding | A-coded |
| Connection thread | M12 |
| Contact surface | Gold-plated |
| Tightening torque | 1 Nm |
| Core cross-section | 0.25 mm ² |
| Housing main material | Brass, nickel-plated |
| Type of mounting | Front mounting |
| Nominal voltage | 30 V |
| Nominal current | 2 A |
| Protection degree | IP67, when screwed in |
| Plugging cycles | ≥ 100 |
| Basic material | PUR |

SAIE-M12S-8-0.5U-M16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|-----------------------------------|---|------|--|
| Rated voltage | 250 V (4-pole)/ 60 V (5-pole)/ 30 V (8 and 12-pole) | | |
| Rated current | 4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole) | | |
| Wire cross section (Print/Online) | 0.34 (4- and 5-pole)/ 0.25 (8-pole)/ 0.14 (12-pole) | | |
| Connection 1 | M12 | | |
| Connection 2 | Flying wires | | |
| Strand / cable length | 0.5 m | | |
| Mounting thread | M 16 x 1.5 | | |
| Mounting torque range | 2 Nm | | |
| Mounting torque | max. | 2 Nm | |
| Temperature range of housing | -30...+90 °C | | |
| Conductor O.D. | - | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC003570 | ETIM 9.0 | EC003570 |
| ETIM 10.0 | EC003570 | ECLASS 14.0 | 27-44-01-03 |
| ECLASS 15.0 | 27-44-01-03 | | |

SAIE-M12S-8-0.5U-M16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Pole scheme

