


SAIE-M12B-8-0.5U-PG9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, M12, Female socket, straight, Mounting thread: PG 9, Number of poles: 8, Strand / cable length: 0.5 m, Front mounting
Order No.	1861270000
Type	SAIE-M12B-8-0.5U-PG9
GTIN (EAN)	4032248419340
Qty.	1 items

SAIE-M12B-8-0.5U-PG9

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

Dimensions and weights

Net weight 33 g

Environmental Product Compliance

RoHS Compliance Status Compliant

REACH SVHC Lead 7439-92-1

SCIP ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical specifications for cable

PE function	No	Core cross-section	0.25 mm ²
Wire cross section (Print/Online)	0.34 (4- and 5-pole)/ 0.25 (8-pole)	Strand / cable length	0.5 m
Colour coding	white, brown, green, yellow, grey, pink, blue, red	Number of poles	8

Technical data customisable plug-in connectors

Number of poles	8	Coding	A-coded
Contact surface	Gold-plated	Housing main material	Zinc diecast
Nominal voltage	30 V	Nominal current	2 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Cable gland	PG 9	Rated current	4 A (4- and 5-pole) / 2 A (8-pole)
Temperature range of housing	-30...+90 °C		

Standards

Connector standard IEC 61076-2-101

General data

Number of poles	8
Coding	A-coded
Connection thread	M12
Contact surface	Gold-plated
Tightening torque	1 Nm
Core cross-section	0.25 mm ²
Housing main material	Zinc diecast
Type of mounting	Front mounting
Nominal voltage	30 V
Nominal current	2 A
Protection degree	IP67, when screwed in
Plugging cycles	≥ 100
Cable gland	PG 9

SAIE-M12B-8-0.5U-PG9

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Basic material	PVC		
Rated voltage	250 V (4-pole) / 60 V (5-pole) / 30 V (8-pole)		
Rated current	4 A (4- and 5-pole) / 2 A (8-pole)		
Wire cross section (Print/Online)	0.34 (4- and 5-pole)/ 0.25 (8-pole)		
Connection 1	M12		
Connection 2	Flying wires		
Strand / cable length	0.5 m		
Mounting thread	PG 9		
Mounting torque range	2 Nm		
Mounting torque	max.	2 Nm	
Temperature range of housing	-30...+90 °C		
Conductor O.D.	-		


Classifications

ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		

Wiring diagram



Pole scheme



SAIE-M12B-8-0.5U-PG9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU PG9-MS	Version	
Order No.	1694080000	SKMU MS (brass locknut), Locknut, PG 9, 2.8 mm, Brass, nickel-plated	
GTIN (EAN)	4008190872243		
Qty.	100 ST		