

## HDC CM HV 3 FC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The CM 3 HV module is an additional trend-setting expansion of the CM3 module line.

The CM 3 HV module is assembled with crimp contacts.

The crimp contact features a stainless steel spring. The provides a secure snap-in contact with the module.

A customized contact removal tool is available for removing the contacts.

The power modules can be ordered with or without the integrated module release aid. A removal tool is available for modules that do not have the integrated module release aid.

### General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	<a href="#">1862060000</a>
Type	HDC CM HV 3 FC
GTIN (EAN)	4032248425495
Qty.	10 items

## HDC CM HV 3 FC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

## Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	43 mm	Height (inches)	1.6929 inch
Width	11.4 mm	Width (inches)	0.4488 inch
Net weight	7.6 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

## ConCept Pneumatic module

UL 94 flammability rating	V-0	Colour	beige
---------------------------	-----	--------	-------

## Dimensions

Width	11.4 mm	Total length base	34 mm
Height of socket	43 mm		

## General data

Number of poles	3	Type of connection	Crimp connection
UL 94 flammability rating	V-0	Volume resistance	≤1 mΩ
Colour	beige	Insulation resistance	1012 Ω
Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)	Type	Female
Surge voltage category	III	Pollution severity	3
Basic material	Polycarbonate, glass fibre reinforced	Series	ConCept module
Rated voltage (DIN EN 61984)	1000 V	Rated impulse voltage (DIN EN 61984)	8 kV
Rated current (DIN EN 61984)	57 A	Free from halogens	false
Low smoke acc. DIN EN 45545-2	Yes		

## Connection data PE

Connection type PE	Screw connection via module frame
--------------------	-----------------------------------

## Version

Wire connection cross section AWG, max.	AWG 7	Stripping length, rated connection	10 mm
Type of connection	Crimp connection	Volume resistance	≤1 mΩ

**HDC CM HV 3 FC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

Wire connection cross section AWG, min.	AWG 16	Conductor cross-section, max.	10 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Basic material	Polycarbonate, glass fibre reinforced

**Classifications**

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		

**Drawings**

