

HDC CM HV 3 MC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The CM 3 HV module is an additional trend-setting expansion of the CM3 module line.

The CM 3 HV module is assembled with crimp contacts. The crimp contact features a stainless steel spring. The provides a secure snap-in contact with the module.

A customized contact removal tool is available for removing the contacts.

The power modules can be ordered with or without the integrated module release aid. A removal tool is available for modules that do not have the integrated module release aid.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1862080000
Type	HDC CM HV 3 MC
GTIN (EAN)	4032248425518
Qty.	10 items

HDC CM HV 3 MC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	43.5 mm	Height (inches)	1.7126 inch
Width	11.4 mm	Width (inches)	0.4488 inch
Net weight	8.3 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

ConCept Pneumatic module

UL 94 flammability rating	V-0	Colour	beige
---------------------------	-----	--------	-------

Dimensions

Width	11.4 mm	Total length base	34 mm
Height of plug	43.5 mm		

General data

Number of poles	3	Type of connection	Crimp connection
UL 94 flammability rating	V-0	Volume resistance	≤1 mΩ
Colour	beige	Insulation resistance	1012 Ω
Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)	Type	Pin
Surge voltage category	III	Pollution severity	3
Basic material	Polycarbonate, glass fibre reinforced	Series	ConCept module
Rated voltage (DIN EN 61984)	1000 V	Rated impulse voltage (DIN EN 61984)	8 kV
Rated current (DIN EN 61984)	57 A	Free from halogens	false
Low smoke acc. DIN EN 45545-2	Yes		

Connection data PE

Connection type PE	Screw connection via module frame
--------------------	-----------------------------------

Version

Wire connection cross section AWG, max.	AWG 7	Stripping length, rated connection	10 mm
Type of connection	Crimp connection	Volume resistance	≤1 mΩ

HDC CM HV 3 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Wire connection cross section AWG, min.	AWG 16	Conductor cross-section, max.	10 mm ²
Conductor cross-section, min.	1.5 mm ²	Basic material	Polycarbonate, glass fibre reinforced

Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		

HDC CM HV 3 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

